


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION






COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.


REVISIONS

LTR	DESCRIPTION	DATE	DWN	APVD
0	RE-ISSUED UTILUX DRAWING	12 FEB 08	MMI	WR



WEDGE LENGTH

3.5 REF		H2097
5.0 REF		H2097A
6.5 REF		H2097B



MOUNTING APERTURE

NOTE: SUITABLE FOR PANEL THICKNESS UP TO 2mm

* DATA IN THIS TABLE SHOULD BE USED FOR GUIDANCE ONLY. DUE TO DIFFERING CABLE MATERIALS AND STRUCTURES, THE SELECTED GROMMET AND APERTURE SIZE SHOULD BE VERIFIED BY PRACTICAL EXPERIMENTATION BEFORE DESIGN IS FINALISED.

9.8-10.3	CORD GRIP GROMMET (H2097)	1-1627229-7	17.3	14.7
8.5-9.7	CORD GRIP GROMMET (H2097A)	1-1627229-2	17.3	14.7
6.4-8.4	CORD GRIP GROMMET (H2097A)	1-1627229-2	15.2	14.3
5.9-6.3	CORD GRIP GROMMET (H2097B)	1-1627229-4	15.2	14.3
CABLE O/D*	DESCRIPTION	PART No	A	B
			APERTURE*	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: M. INSTANCE 12 FEB 08	Kingsgrove AUSTRALIA		
ALL DIMENSIONS IN mm:		CHK: H. THAI 12 FEB 08			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: W. RIEDE 12 FEB 08	NAME: CORD GRIP GROMMET (H2097)		
DIMENSION(mm) TOLERANCE(mm)		PRODUCT SPEC:			
LESS THAN 10 ±0.20		APPLICATION SPEC:			
OVER 10 TO 30 ±0.30		WEIGHT: -	SIZE A3	CAGE CODE	DRAWING NO C-1627229
OVER 30 TO 80 ±0.45					RESTRICTED TO -
MATERIAL BLACK NYLON	FINISH -	CUSTOMER DRAWING			
		SCALE NTS	SHEET 1 OF 1	REV 0	