

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0503253502](#)
Status: **Obsolete**
Description: Spade Tongue Terminal for 16-22 AWG, Closed Insulated Vinyl Flared Barrel, Red, Stud Size 5 (M3), Oxygen-Free Copper, Length 19.50mm (.768")

Documents:
[Drawing \(PDF\)](#)

General

Product Family	Ring and Spade Terminals
Series	50325
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Product Name	VFY (Spade Vinyl Flared)
Type	Spade

Physical

Barrel Type	Closed - Brazed
Color - Resin	Red
Insulation	PVC
Material - Plating Mating	Tin
Packaging Type	Bag
Stud Size	5 (M3)
Wire Size AWG	16, 18, 20, 22
Wire Size mm²	0.25 - 1.65

Material Info

Reference - Drawing Numbers

Product Specification	PS-50325-002
Sales Drawing	SD-50325-001




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[50325Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION