NOTE: UNLESS OTHERWISE SPECIFIED

1. RETRACTABLE SHROUDED BANANA PLUG
BODY: NICKEL PLATED BERYLLIUM-COPPER
INSULATOR: POLYACETAL
PLUG: NICKEL PLATED BRASS
ELECTRICAL DATA:
DIELECTRIC WITHSTANDING
VOLTAGE: 1 kV
MAX. CURRENT: 15 AMPS

2. WIRE: 18 AWG P.V.C. INSULATION
65X36 TINNED COPPER, INSULATION
DIA. .144" THICKNESS .045" MAX.
WORKING VOLTAGE 5,000 VOLTS
MAX TEMP. 105C. MAX CURRENT
5 AMPS.

ZONE	LTR		DATE	APPROVED





		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS ± DECIMALS .XX ± .XXX ± ANGLES ±	CONTRACT NO.		E-Z-HOOK ARCADIA, CA 91006
			APPROVALS	DATE	
		MATERIAL SEE NOTE	DRAWN S.B.W.	11/03	RETRACTABLE SHROUDED BANANA PLUG JUMPER
			CHECKED		
		FINISH SEE NOTE			SIZE B · CODE IDENT NO. 08505 · DRAWING NO. 9871-LENGTH
NEXT ASSY	USED ON				
APPLICATION		DO NOT SCALE DRAWING			SCALE FULL · SHEET 1 OF 1