

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202010048](#)
Status: **Active**
Overview: [Brad Ultra-Lock Connection System](#)
Description: Ultra-Lock (M12) Single-Ended Cordset, 8 Poles, Male (Straight) to Pigtail, 24 AWG, PUR Cable, 4.0m (13.12') Length, Yellow


Documents:
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Cordsets
Series	120201
Connector End A	Ultra-Lock (M12)
Connector End B	Pigtail
IP Rating	IP68
Material - Contact	Copper Alloy
Overview	Brad Ultra-Lock Connection System
Product Name	Ultra-Lock (M12)
Protocol	N/A
Region	America
Type	Single Ended
UPC	78678809506

Physical	
Cable Diameter	6.60mm (.260")
Cable Length	4.0m (13.12')
Color - Cable Jacket	Yellow
Coupling Style	Push to Lock
Gender	Male-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	Straight to Pigtail
Poles	8
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	24
Wire/Cable Type	EU Cable

Electrical	
Current - Maximum per Contact	2.0A
Voltage - Maximum	30V
Material Info	
Engineering Number	W08S06P19M040
Reference - Drawing Numbers	
Sales Drawing	SD-120083-022



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[120201](#) Series