THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST
DY	-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	AJ	REVISED PER ECR-08-010155	22APR08	SYJ	LSF



REMARKS	QTY	HEIGHT TYPE	H	G	F	E	D	C	B	A	POS	CONN P/N	PART NO.
0.00076 MIN GOLD PLATING (30u INCHES GOLD PLATING)							61.8	88	84.4	42.2	140	-6	6- -6
							53.8	72	68.4	34.2	120	-5	6- -5
	550		16				45.8	72	68.4	34.2	100	-4	6- -4
							37.8	56	52.4	26.2	80	-3	6- -3
							29.8	44	40.4	20.2	60	-2	6- -2
	800	6H	12	17	5.85	6.25	21.8	32	28.4	14.2	40	84615-1	6-177986-1
							69.8				160	-8	5- -8
							61.8	88	84.4	42.2	140	-6	5- -6
							53.8				120	-5	5- -5
	650		16				45.8	72	68.4	34.2	100	-4	5- -4
							37.8	56	52.4	26.2	80	-3	5- -3
							29.8	44	40.4	20.2	60	-2	5- -2
	900	5H	12	17	4.85	5.25	21.8	32	28.4	14.2	40	84614-1	5-177986-1
0.00002 MIN GOLD PLATING (7.8u INCHES GOLD PLATING)							85.8				200	1- -0	4- -0
							77.8	104	100.4	50.2	180	-9	3- -9
							69.8				160	-8	3- -8
							61.8	88	84.4	42.2	140	-6	3- -6
							53.8				120	-5	3- -5
	400		16				45.8	72	68.4	34.2	100	-4	3- -4
							37.8	56	52.4	26.2	80	-3	3- -3
							29.8	44	40.4	20.2	60	-2	3- -2
	600	8H	12	17	7.85	8.25	21.8	32	28.4	14.2	40	179031-1	3-177986-1
							85.8				200	1- -0	3- -0
							77.8	104	100.4	50.2	180	-9	2- -9
							69.8				160	-8	2- -8
							61.8	88	84.4	42.2	140	-6	2- -6
							53.8				120	-5	2- -5
	450		16				45.8	72	68.4	34.2	100	-4	2- -4
							37.8	56	52.4	26.2	80	-3	2- -3
							29.8	44	40.4	20.2	60	-2	2- -2
	700	7H	12	17	6.85	7.25	21.8	32	28.4	14.2	40	179030-1	2-177986-1
							61.8	88	84.4	42.2	140	-6	1- -6
							53.8				120	-5	1- -5
	550		16				45.8	72	68.4	34.2	100	-4	1- -4
							37.8	56	52.4	26.2	80	-3	1- -3
							29.8	44	40.4	20.2	60	-2	1- -2
	800	6H	12	17	5.85	6.25	21.8	32	28.4	14.2	40	179029-1	1-177986-1
							69.8				160	-8	-8
							61.8	88	84.4	42.2	140	-6	-6
							53.8				120	-5	-5
	650		16				45.8	72	68.4	34.2	100	-4	-4
							37.8	56	52.4	26.2	80	-3	-3
							29.8	44	40.4	20.2	60	-2	-2
	900	5H	12	17	4.85	5.25	21.8	32	28.4	14.2	40	177984-1	177986-1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±0.3
2 PLC	±0.25
3 PLC	±0.2
4 PLC	±-
ANGLES	±3°

MATERIAL -
FINISH -

DWN T.KUSUHARA 8FEB93
CHK I.ENOMOTO
APVD SF LFONG
PRODUCT SPEC 108-5390
APPLICATION SPEC 114-5254
WEIGHT -

Tyco Electronics
TYCO ELECTRONICS SINGAPORE

NAME
PLUG ASSEMBLY (0.5 BOSS LENGTH) FOR FH 0.8 B-T-B CONN. ON TAPING

SIZE	CAGE CODE	DRAWING NO
A3	00779	C-177986

CUSTOMER DRAWING
SCALE 2:1 SHEET 1 OF 1 REV AJ

AMP 1470-19 REV 09MAY94

Pro/ENGINEER DRAWING