





REV. 0
DCO 143596

COIL: @ 25 $^\circ$ C
 RESISTANCE 850 OHMS $\pm$ 10%
 NOMINAL VOLTAGE 12.0 VDC
 MUST OPERATE 7.8 VDC
 MUST RELEASE 1.3 VDC MIN

ENVIRONMENT:
 VIBRATION 10 Hz TO 3000 Hz @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 $^\circ$ C TO +125 $^\circ$ C
 NOTES: OPERATE TIME 4.0 MS MAX.
RELEASE TIME 7.5 MS MAX.
CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB 21 JUN 02

CK. *[Signature]* 6/21/02

CII Technologies
 advanced control electronic solutions

CUST. CII
 CUST. NO. STANDARD REV.

"MSDD" RELAY

MSCDD-12