THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	WEIGHT (APPROX.)
NK6PPG12WY	1.25 lb (567 g)



RETENTION CAP SNAPS ONTO CONNECTOR
ONE CAP PER CONNECTOR



NOTES:
1. MATERIAL:
   PANEL HOUSING: STEEL/BLACK POWDER COAT
   RJ45 MODULE: THERMOPLASTIC RESIN UL94V-0
   PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0
   BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B
   RETENTION CAP: THERMOPLASTIC RESIN UL94V-0
2. 12 PORT PATCH PANEL WITH TWO 6 POSITION BEZELS ASSEMBLIES, 8 WIRES PER JACK ASSEMBLY.
3. THE PATCH PANEL IS DESIGNED TO SNAP INTO A STANDARD S89D WALL MOUNT BRACKET.
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
5. USE 110 STYLE TERMINATION TOOL FOR PUNCH DOWN.
6. RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.

MODEL FILENAME: M02088AG_12_PORT_03
DRAWING FILENAME: M02479MO_DC328_00A.PRT
SIZE: A

TITLE: NETKEY CAT6 12 PORT PATCH PANEL CUSTOMER DRAWING

PANDUIT™ CORP.
TINLEY PARK, IL 60477

I.I. NUMBER
PRODUCT SPEC
WORK INSTRUCTION

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) ± .03 (.XXX) ± .005
(.XX) ± .01 ANGLES ± 1°

SCALE: .25:1

DRAWN BY: NER
DATE: 3-22-06
CHK'D:
REVIEW DRAWING NUMBERS

PART NO.: NK6PPG12WY
DRAWING NO.: 02479-328

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
R	3-22-06			RELEASED TO PRODUCTION	02479-328			