TIGER BUY™ CONTACT

FLEXIBLE ELEVATED & SELF-NESTING SOCKETS



(2.00 mm) .0787" PITCH • ESQT/ESQT (-368)/PTHF SERIES

ESQT

Board Mates:
TMMH, TMM, MTMM, MMT, TW, LTMM, ZLTMM, ESQT, PTT, TSH, TMMS

Cable Mates:
TCMD

SPECIFICATIONS

Insulator Material:
Black Liquid Crystal Polymer
Contact Material:
Phosphor Bronze
Plating:
Sn or Au over
50 µ" (1.27 µm) Ni
Current Rating (ESQT/TMMH):
4.5 A per pin
(2 pins powered)
Operating Temp Range:
-55 °C to +125 °C
Insertion Depth:
(2.62 mm) .103" to
(5.03 mm) .198" with
(0.38 mm) .015" wipe
Max Cycles:
100 with 10 µ" (0.25 µm) Au
Lead–Free Solderable:
Yes, for -S, -D & -Q
(Wave only for -T, -5 & -6)

ESQT	-	1	NO. PINS PER ROW	-	LEAD STYLE	-	PLATING OPTION	-	ROW OPTION	-	BODY HEIGHT	-	OTHER OPTION
			02 thru 50		Specify LEAD STYLE from chart		–F = Gold flash on contact, Matte Tin on tail –L = 10 µ" (0.25 µm) Gold on contact, Matte Tin on tail –M = 20 µ" (0.51 µm) Gold on contact, Matte Tin on tail –GF = 15 µ" (0.38 µm) Gold on contact, Gold flash on tail (Recommended for self-nesting) (–02 lead style only)		–S = Single Row –D = Double Row –T = Triple Row –Q = Quad Row –5 = Five Row –6 = Six Row		–"XXX" = Body Height (in inches) (7.87 mm) .310" minimum for –S, –D, –Q (9.53 mm) .375" minimum for –T, –5, –6		–"XXX" = Polarized Position (Indicate position number)



LEAD STYLE	A	MAX TAIL	MAX BODY HEIGHT
–02	(21.59) .850	(13.72) .540	(20.32) .800
–03	(11.63) .458	(3.76) .148	(10.36) .408



ESQT (-368)/PTHF

Mates:
ESQT, PTHF

SPECIFICATIONS

Insulator Material:
Black Liquid Crystal Polymer (ESQT-368)
Black High Temp Nylon (PTHF)
Contact Material:
Phosphor Bronze
Plating:
Au or Sn over
50 µ" (1.27 µm) Ni
Operating Temp Range:
-55 °C to +125 °C
Max Cycles:
100 with 10 µ" (0.25 µm) Au
Lead–Free Solderable:
Yes (ESQT-368)

SERIES	-	1	NO. PINS PER ROW	-	LEAD STYLE	-	PLATING OPTION	-	Q	-	368
ESQT = Solder Tails PTHF = Press-fit Tails			30		Specify LEAD STYLE from chart		–GF = 15 µ" (0.38 µm) Gold on contact, Gold flash on tail (–02 Lead Style only) –M = 20 µ" (0.51 µm) Gold on contact, Matte Tin on tail (–03 Lead Style only)				

EMBEDDED-PC PC/104 MODULES

LEAD STYLE	ESQT		PTHF	
	A	B	A	B
–02	(21.59) .850	(12.24) .482	(21.59) .850	(12.24) .482
–03	(11.63) .458	(2.29) .090	(12.34) .486	(3.00) .118





ESQT (–368) SERIES

PTHF SERIES

TOOLING

Press-Fit
CAT-PT-PT-130-A-4

For more information, visit
www.samtec.com/tooling

Note:
This Series is non-standard, non-returnable.

samtec.com?ESQT or samtec.com?PTHF

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.