ローレットつまみ

RoHS　ステンレス　カラバリ　CAD

KNURLED KNOB FASTENERS

A-1038 ステンレス製　**A-1038-TMP** ステンレス製　**AP-38** プラスチック製　**A-38** 黄銅製

A-1038

A-1038-TMP

AP-38-2-Ivory（特注色）
アイボリー (custom-made color)

AP-38-3-Black（標準色）
ブラック (standard color)

〔A-1038・A-1038-TMP・A-38〕



〔AP-38〕



特　徴　Feature

仕　様

〔A-1038〕●材　　質：ステンレス鋼（SUS304）
●表面仕上：鏡面バフ研磨

〔A-1038-TMP〕●材　　質：ステンレス鋼（SUS304）
●表面仕上：電解研磨（TMP）

〔AP-38〕●材　　質：頭部／ABS樹脂
ねじ部／快削黄銅棒（3604BD）
●表面仕上：ねじ部／ニッケルめっき（MBNi）

〔A-38〕●材　　質：快削黄銅棒（3602BD）
●表面仕上：クロムめっき（MBCr）
●付 属 品：S.W.・ナット

用　途　●配分電盤・制御盤・小型ボックス

納　期　●標準在庫品

備　考　●他のカラーも製作致します。（AP-38）

Specifications

〔A-1038〕●Material: Stainless steel (SUS304)
●Finish: Mirror surface buffing

〔A-1038-TMP〕●Material: Stainless steel (SUS304)
●Finish: Electrolytic polishing (TMP)

〔AP-38〕●Material: Head: ABS resin
Screw: Free cutting brass bar (C3604BD)
●Finish: Screw: Nickel plating (MBNi)

〔A-38〕●Material: Free cutting brass bar (C3602BD)
●Finish: Chrome plating (MZCr)
●Accessories: S.W. and nut

Specific use　●Distribution, control boards and small boxes.

商品番号 Product No.	RoHS	CAD	材　質 Material	L_1	L_2	L_3	ϕD_1	ϕD_2	M	製品質量(g) Mass	コード Code	単　価 Price	量販価格 Bulk Price 数量 Quantity	単価 Price
A-1038	●	2D/3D	SUS304	図面参照 See the drawings						40	01558	¥500	20個～	¥480
NEW A-1038-TMP	●	3D	SUS304							40	04616	¥750	20個～	¥720
A-38	●	2D/3D	黄銅 Brass							40	00137	¥240	25個～	¥230
AP-38-1-Black	●	2D/3D	ABS樹脂	19	11	9	22	11	M6	9	01366	¥190	50個～	¥182
AP-38-2-Black	●	2D/3D		15	10	5	18	9	M5	5	01367	¥170	50個～	¥163
AP-38-3-Black	●	2D/3D		12	8	2	15	8	M4	3	01368	¥160	50個～	¥154

●：RoHS指令対応品　▲：RoHS指令に対応可能です。　※大量のご注文は更にお安くなります。