Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'F5LE10E-NM10'**

Your search criteria matched only one product, shown below

F5LE10E-NM10

• Colour-specific keys mechanically and visually distinguish connections to prevent positive and negative unintentional insertion into unlike keyed or non-keyed ports and allows design flexibility and versatility for a more discrete network
• Factory terminated and 100% tested for insertion loss (all) and return loss (10Gig™ and SM). Assures high performance for increased up-time and lower cost of ownership
• Low smoke zero halogen meets IEC-60332 (LSZH) flame rating for standard compliant safety
• Singlemode endfaces UPC polished (55dB min. return loss) ensures a high quality endface for higher return loss to meet application requirements
• Every singlemode endface is 100% factory inspected in compliance with Telcordia GR-326-CORE, Issue 3 requirements to assure high performance
• Keyed LC 10Gig™ Patch Cords and Pigtails are tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10Gb/s for link lengths up to 300 meters for OM3 at 850nm to assure high performance and reliability
• Test data supplied with each patch cord and pigtail establishes a performance reference to streamline maintenance and troubleshooting

Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact Customer Service for actual lead times.
Additonal keyed colors include the following: G– Violet, H– Aqua, J– Rose, K– Slate, L– Brown, P– White, Q– Charcoal, R– Lavender, S– Peach, T– Steel Blue, V– Maroon and W– Mint.

Part Number	F5LE10E-NM10
RoHS Compliancy Status	RoHS directive is not applicable
Note	Intended for use in fixed installations which are outside the scope of RoHS.
Part Description	LC (keyed E- orange) to pigtail, LSZH, multimode duplex patch cord, 1.6mm jacketed cable (one duplex keyed LC connector on one end and pigtail on other end)– 50/125?m.
Product Type	Keyed LSZH Patch Cords
Length (m)	10
Fiber Compatibility	50/125µ m
Fiber Cable Size	1.6mm
Fiber Cable Type	Jacketed
Connector 1 Type	LC Connector- Keyed E (Orange)
Connector 2 Type	Pigtail
Flammability Rating	LSZH (Low Smoke Zero Halogen)
Key Type and Color	Keyed E- Orange
Pricing Description	Keyed LC (E-Orange) pigtails, 50um, Duplex, LSZH, 10M
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy