

Customer Information Sheet

DRAWING No.: M50-430XX45

SHEET 2 OF 2


IF IN DOUBT - ASK

(C)


NOT TO SCALE

THIRD ANGLE PROJECTION



ALL DIMENSIONS IN mm



RECOMMENDED PCB LAYOUT
(TOLERANCE = ±0.05)



SPECIFICATIONS:
MATERIAL:
MOULDING = LCP UL94V-0, BLACK
CONTACT = PHOSPHOR BRONZE
FINISH:
CONTACT = GOLD
ELECTRICAL:
CURRENT RATING = 1A
VOLTAGE PROOF = 500V AC FOR ONE MINUTE
CONTACT RESISTANCE = 20mΩ MAX
INSULATION RESISTANCE = 5000MΩ MIN
MECHANICAL:
INSERTION FORCE = 2.00N MAX
WITHDRAWAL FORCE = 0.15N MIN
DURABILITY = 100 CYCLES MIN
ENVIRONMENTAL:
OPERATING TEMPERATURE = -40°C TO +105°C
PACKING:
TUBE
FOR COMPLETE SPECIFICATION, SEE COMPONENT SPECIFICATION C029XX (LATEST ISSUE).



ORDER CODE:
M50-430XX45
No. OF CONTACTS PER ROW: 03 TO 50
FINISH: GOLD ALL OVER CONTACT

NOTES:
1. ALL TOLERANCES ARE ±0.12
UNLESS OTHERWISE STATED.

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.50mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH:

SEE ABOVE

S/AREA:

mm²

TITLE:

1.27mm PITCH DIL
VERTICAL SMT SOCKET ASSY

DRAWING NUMBER:

M50-430XX45

SHT
2 OF 2