

SPECIFICATION

1.Rated Voltage .....12 VDC
2.Operating Voltage .....8~15VDC
3.Max.Rated Current 30mA/12VDC
4.Resonant Frequency .....2300±300Hz
5.Min.Sound Pressure Level.....85dB/10cm
6.Response Time 50ms
7.Case Material .....MPPO
8.Operating Temperature .....-20～+70℃
9.Store Temperature .....-30～+80℃
10.Weight 7g

No.	DESCRIPTION	APPROVED	DATE

TOLERANCES UNLESS NOTED OTHERWISE
.X ±
.XX ±
.XXX ±
90° FORMED ±2°
ANGLES ±1°

FIRST ANGLE PROJECTION

APPROVALS	DATE
DRAWN	
CHECKED	
APPROVED	05.04.26

KEPO ELECTRONIC CO., LTD.
http://www.kepo.com.tw

Magnetic Buzzer
KPX-1612A

UNIT	DWG NO.		
mm	KP3.840.659		
SCALE	SHEET	VER	
NOT TO SCALE		1.1	