




REV. B
DCO 300860

TOLERANCES $\pm .010"$ - UNLESS
OTHERWISE SPECIFIED

COIL: @ 25°C

RESISTANCE 320 OHMS $\pm 10\%$

NOMINAL VOLTAGE 28 VDC

MUST OPERATE 13.5 VDC MAX.

MUST RELEASE 5.5 VDC MAX., 2.3 VDC MIN.

ENVIRONMENT:

VIBRATION 33 Hz TO 3000 Hz @ 20 g's

SHOCK 200 g's 6 MS. DURATION


TEMPERATURE -70 °C TO +125 °C

NOTES: OPERATE, RELEASE 10 MS MAX.

CONTACT BOUNCE 1 MS MAX.

CUSTOMER DATA SHEET

A1 - X2 A2 A3



CONTACT RATING:
25 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE
50,000 OPERATIONS

DR. B.D. 21MAY2008 CK. J.M.B. 5/21/08

Tyco Electronics

©COPYRIGHT 2005
TYCO ELECTRONICS CORPORATION
ALL INTERNATIONAL RIGHTS RESERVED

CUST. CATALOG ITEM

CUST. NO. ---- REV. ----

TE NUMBER

7-1617748-1

CII PART NUMBER

FCA-125-CW3