

REV. 1 7/9/92

COIL: @ +25° C

RESISTANCE	675 OHMS ± 10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	13.0 VDC
MUST RELEASE	1.5 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 100 g's 6 ± 1 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES:

CUSTOMER DATA SHEET



CONTACT RATING: 2 AMPS 30 VDC
RESISTIVE 1 AMP 30 VDC INDUCTIVE
100,000 OPERATIONS

DR. R.B. 7/9/92 CK. 7/9/92

COMMUNICATIONS INSTRUMENTS, INC.

CUST. HI-G
CUST. NO. 2B-1B-126

TYPE "FW" RELAY

FW1193G01