

Part Number . . . **BFG.0B.100.PCSG**

Size/Series 0B / B

[Request a quote](#)


MECHANICAL DETAILS

Shell Style/Model	BFG*: Cap for plug (G key)
Keying	1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Housing Material	POM (Polyoxymethylene) shell without treatment, silicone gasket
Cable Fixing	∅ : 0 - 0 mm
Variant	:

PERFORMANCE DETAILS

OTHER CHARACTERISTICS

Endurance (Shell)	3839 mating cycles
Temp (min)	-55°C deg
Temp (max)	+250°C deg
Humidity (max):	<=95% [at 60 deg C /140 F]
Vibration:	15 g [10 Hz - 2000 Hz]
Shock Resistance:	100 g [6 ms]
Salt Spray Corrosion:	>144 hr
Climatical Category:	50/175/21
Shielding (min):	75 dB (10 MHz)
Shielding (min):	40 dB (1 GHz)
IP Rating	50
Catalog	

[Copyright](#) [Privacy policy](#) [Product safety](#)