









9000 SERIES - MINIATURE MOMENTARY PUSHBUTTON SWITCHES

OPTION DRAWINGS & SPECIAL OPTIONS

CAPS Note: replace last '0' in p/n with color code. (order separately)

 5.00 DCA (.195) 3.25 (.127) 4.00 (.157)	 8.00 DCA (.314 DCA) 3.00 (.118) 6.35 (.250)	 9.40 DCA (.370) 3.00 (.118) 6.35 (.250)	 10.00 DCA (.390) 3.00 (.118) 7.50 (.295)																			
 15.00 DCA (.590 DCA) 10.00 (.390) 5.00 (.118)	 11.50x11.50 (.452 SQ) 3.00 (.118) 4.00 (.157)	 11 x5x11 x5 (.4x2 SQ) 5.00 (.195) 6.00 (.235)		<table><tr><th colspan="2">Colors</th></tr><tr><td>1</td><td>blue</td></tr><tr><td>2</td><td>black</td></tr><tr><td>3</td><td>green</td></tr><tr><td>4</td><td>grey</td></tr><tr><td>5</td><td>yellow</td></tr><tr><td>6</td><td>red</td></tr><tr><td>7/1</td><td>white</td></tr><tr><td>9</td><td>orange</td></tr></table>	Colors		1	blue	2	black	3	green	4	grey	5	yellow	6	red	7/1	white	9	orange
Colors																						
1	blue																					
2	black																					
3	green																					
4	grey																					
5	yellow																					
6	red																					
7/1	white																					
9	orange																					

DRESS NUTS Chrome plated. Order separately.

 U1636 (for cap U1140)	 U825 (for cap U630)	 U840 (for cap U480)
---	---	---

SPECIAL OPTIONS

F Tin plated terminals (for p.c. terminals only).

X601 Silver plated brass contacts
 Contact ratings: 0.2A 250VAC, 0.4A 125VAC or 0.5A 30VDC
 Electric life: 20,000 cycles minimum.
 Minimum quantity: 5,000 pieces.

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

C