








SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	G±0.25
09	30.81	24.99	16.96	16.79	10.96	5.90
15	39.14	33.32	25.18	25.12	19.18	5.90
25	53.03	47.04	39.12	38.84	33.12	5.70
37	69.32	63.50	55.68	55.30	49.68	5.70



PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



4 = Performance level PL3 ≥ 200 OPERATIONS —
6 = Performance level PL1 ≥ 500 OPERATIONS —

V = SCREWLOCK Threaded UNC 4.40 sellers

SHELL	LEAD FREE PART NUMBER	TIN LEAD PART NUMBER	DESIGNATIONS
09	D09P24A6GV00LF	D09P24A6GV00	HEADER 9 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
15	D15P24A6GV00LF	D15P24A6GV00	HEADER 15 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
25	D25P24A6GV00LF	D25P24A6GV00	HEADER 25 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
37	D37P24A*GV00LF	D37P24A*GV00	HEADER 37 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.

4 = Performance level PL3 ≥ 200 OPERATIONS —
6 = Performance level PL1 ≥ 500 OPERATIONS —



SHELL	LEAD FREE PART NUMBER	TIN LEAD PART NUMBER	DESIGNATIONS
09	D09P24A*GI00LF	D09P24A*GI00	HEADER 9 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
15	D15P24A*GI00LF	D15P24A*GI00	HEADER 15 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
25	D25P24A*GI00LF	D25P24A*GI00	HEADER 25 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
37	D37P24A*GI00LF	D37P24A*GI00	HEADER 37 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.

I = SCREWLOCK Threaded M3

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0000

European Views

www.fciconnect.com				surface ISO 1302		tolerance std ISO 406 ISO 1101	projection 		mm 		
				TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	JARRY	1995/08/11	ANGULAR	LINEAR		0.X	±0.1	size	A3	Scale	2
Eng	PESSON	1995/08/11	NIRMAL GEORGE	2010-02-23	0.XX	±2	±0.1	ECN	110-0059		
Chr	SUDHIR VARMA	2010-02-23				Product family	D-SUB	Spec ref	-		
Appr											
FCI				HEADER DELTA D STD EUROPE				Rev.			
e				C01-8646-0816				F			
HEADER DELTA D STD EUROPE				CUSTOMER				sheet 1 of 1			
catalog no				-							
rev	ecn no	dr	date								
A	-	BAR	2003/04/16								
B	LS05-001	MPE	2005/03/14								
C	LS05-0056	LGO	2005/07/07								
D	LS06-0097	LGO	2006/07/28								
E	109-0268	NG	2009-11-24								
F	110-0059	NG	2010-02-23								
-	-	-	-								

