




# MISCELLANEOUS



## Utility Compartment Box




- 10"x4.75"x1.5" (LxWxH)
- Up to 12 compartment
- Removable partitions




| Description             | Part No. |
|-------------------------|----------|
| Utility Compartment Box | 900-039  |

## Utility Component Storage Box




- 8.25"x4.7"x1.25" (LxWxH)
- Material: P.P.




| Description                   | Part No. |
|-------------------------------|----------|
| Utility Component Storage Box | 902-112  |

## Utility Compartment Box




- 11"x7"x1.75" (LxWxH)
- Removable partitions
- 15 pcs dividers included



| Description             | Part No. |
|-------------------------|----------|
| Utility Compartment Box | 900-040  |


## Utility Compartment Box



- 6.5"x3.75"x1.75" (LxWxH)
- 5 compartments on one side, 8 on the other
- Lid opens on both sides doubling the number of items to be stored

| Description             | Part No. |
|-------------------------|----------|
| Utility Compartment Box | 900-043  |

## Utility Compartment Box




- 8"x5.25"x1.5" (LxWxH)
- Removable partitions
- 12 pcs dividers included



| Description             | Part No. |
|-------------------------|----------|
| Utility Compartment Box | 900-041  |

## Utility Component Storage Box



- 3"x3-3/16"x13/16" (LxWxH)
- Material: P.P.




| Description                   | Part No. |
|-------------------------------|----------|
| Utility Component Storage Box | 902-113  |

## Die Cast Aluminum Enclosures


Item #: 900-162A



Item #: 900-162B




Item #: 900-162C



- Heavy-duty enclosures
- High-quality die cast aluminum
- Channeled walls for convenient PCB mounting
- Act as excellent heat sink

| Description       | Part No. |
|-------------------|----------|
| 3.81"x1.96"x0.98" | 900-162A |
| 4.64"x2.36"x1.57" | 900-162B |
| 7.36"x4.21"x2.36" | 900-162C |

## Utility Component Storage Box



Material: P.P.

- 7-3/8"x4-5/8"x7/8" (LxWxH)
- Material: P.P.



Terminals not included

| Description                   | Part No. |
|-------------------------------|----------|
| Utility Component Storage Box | 900-114  |

## Instrument Cases

Item #: 900-164A



Item #: 900-164B

- Durable ABS cases allow for various PCB mounting positions
- Adhesive feet and screws are included
- 900-164B has ventilation slots and speaker recess

| Description       | Part No. |
|-------------------|----------|
| 7.87"x6.29"x2.51" | 900-164A |
| 9.84"x7.48"x3.07" | 900-164B |


## Insertion / Extraction Tool

- For inserting & extracting pins and sockets in connector housing



| Description                 | Part No. |
|-----------------------------|----------|
| Insertion / Extraction Tool | 900-065  |

## Spudger



- Probe & Pick
- Tough nylon glass fiber construction
- Non-conductive - prevents shorting

| Description | Part No. |
|-------------|----------|
| Spudger     | 900-140  |

## Parts Tubes

- 3-pack



| Description | Part No. |
|-------------|----------|
| Parts Tubes | 900-091A |

## Metal Pronged Parts Grabber

Picks up and holds small parts in tight spaces.



| Description             | Part No. |
|-------------------------|----------|
| 4-Pronged Parts Grabber | 902-225  |

## PLCC Extractor

- Spring assisted
- Chip carrier extractor
- Extracts most PLCC's



| Description    | Part No. |
|----------------|----------|
| PLCC Extractor | 900-032  |

## PLCC Extractor

A spring assisted chip carrier extraction tool, specially designed for the safe removal of PLCC's from sockets without damage to component parts.



| Description    | Part No. |
|----------------|----------|
| PLCC Extractor | 902-224  |

## IC Extractor



| Description  | Part No. |
|--------------|----------|
| IC Extractor | 900-258  |

## 3-Pronged Parts Grabber

- Plunger opens prongs



| Description             | Part No. |
|-------------------------|----------|
| 3-Pronged Parts Grabber | 900-094  |

## Long Pick-up Tool with Magnet Tip (24-1/2")

Long Pick-Up Tool with Magnet Tip is an extendable magnetic tool for picking up small metallic objects from inaccessible areas. This Pick-Up Tool has a 24 1/2" flexible stem with a strong magnet at one end.

- Powerful magnet lifts 3.3 lb
- Ideal for home, shop, garage, work place etc.

**New**

Powerful magnet lifts  
**3.3lb**

Pick up small  
metallic  
objects from  
inaccessible  
areas



24 1/2"

| Description                                 | Part No. |
|---------------------------------------------|----------|
| Long Pick-up Tool with Magnet Tip (24-1/2") | 902-255  |


## Push-button Pick-up Tool

- 902-256: Push-Button Pick-Up Tool has a 10-1/2" flexible stem with a small set of jaws at one end.
- 902-257: Long Push-Button Pick-Up Tool has a 23-1/2" flexible stem with a small set of jaws at one end.
- Ideal for home, shop, garage, work place etc.

**New**

23-1/2"

Item #:902-257



10-1/2"

Item #:902-256

| Description                                | Part No. |
|--------------------------------------------|----------|
| Push-Button Pick-Up Tool (10 -1/2" )       | 902-256  |
| Long Push-Button Pick-Up Tool ( 23 -1/2" ) | 902-257  |

**New**

## Knife



| Description               | Part No. |
|---------------------------|----------|
| Knife                     | 900-257  |
| Spare Blades (10 pc pack) | 900-257B |

## Self-Loading Utility Knife

- Segmented, snap-off blades.
- Pocket clip.
- Self-loading - as one blade is discarded, simply pull the slide back and it loads another blade.
- Knife holds three blades.



| Description                               | Part No. |
|-------------------------------------------|----------|
| Self-Loading Utility Knife                | 900-169  |
| Replacement blade for 900-169 (6 pc pack) | 900-169B |

## Electrician's Knife



| Description         | Part No. |
|---------------------|----------|
| Electrician's Knife | 900-178  |

## Utility folding Knife



Item #: 902-261



Item #: 902-253

| Description                         | Part No. |
|-------------------------------------|----------|
| Utility folding knife               | 902-253  |
| Utility knife blades-100 pcs a pack | 902-261  |

## Fuse Puller



- Shock-proof durable plastic
- Serrated grip design to prevent slipping
- Safely removes 0-200A/250V and 0-100A/600V Cartridge fuses

| Description | Part No. |
|-------------|----------|
| Fuse Puller | 900-177  |

## 7-In-1 Multi-Function Pocket Tool Key Chain



- Pocket-sized tools complete with spring-loaded pliers and almost any thing else you might need to get out of a bind.
- These tools include slotted and phillips screwdrivers, a serrated saw, a fruit knife, a mini LED flashlight, and a bottle opener.
- 7-in-1 function is all readily available to assist with your fix-it, snippet, tune-up, and tweak.

OAL: 4"

| Description                                 | Part No. |
|---------------------------------------------|----------|
| 7-In-1 Multi-Function Pocket Tool Key Chain | 902-230  |

## Razor Hobbyist's Knife

Item #: 900-112



Item #: 900-113

| Description                                | Part No. |
|--------------------------------------------|----------|
| Razor Hobbyist's Knife - Small             | 900-112  |
| Replacement Blade for 900-112 (10 pc pack) | 900-112B |
| Razor Hobbyist's Knife - Large             | 900-113  |
| Replacement Blade for 900-113 (10 pc pack) | 900-113B |

## 5 Pc Hook Set


Contains 6 parts 5 different hooks which can be screwed in a handle.



| Description   | Part No. |
|---------------|----------|
| 5 Pc Hook Set | 900-033  |

## Hobby Vise

- Jaw width, 2.4"
- Opens to 2"
- Clamps to any surface up to 1" thick



| Description | Part No. |
|-------------|----------|
| Hobby Vise  | 900-049  |

## Multi-Angle Swivel-Action Vacu-Vise

- Swivels 360° and tilts 90° to desired angle.
- 2-1/2" metal jaws open to 2-1/2" .
- Equipped with slide-on rubber jaw for fragile work.
- 6-1/4" triangular base.
- Aluminum die-cast construction.
- Light weight and durable.



| Description                         | Part No. |
|-------------------------------------|----------|
| Multi-Angle Swivel-Action Vacu-Vise | 902-117  |

## Magnetic, Telescopic Pick-up Tool

- Screwdriver handle style
- Magnetic tip
- Extends to approximately 16" long

| Description                       | Part No. |
|-----------------------------------|----------|
| Magnetic, Telescopic Pick-up Tool | 900-017  |



## Telescoping Magnetic Pick-up Tool

- Strong pick up force of 9 lbs.
- Allows access to "hand-to-reach" parts.
- Telescopes from 6-1/2" to 25-5/8"

| Description                       | Part No. |
|-----------------------------------|----------|
| Telescoping Magnetic Pick-up Tool | 900-212  |



## Inspection Mirror

| Description       | Part No. |
|-------------------|----------|
| Inspection Mirror | 900-255  |



## 2" x 3" Rectangular Inspection Mirror

- Telescopes to 8-1/2"~19-1/4"

| Description                           | Part No. |
|---------------------------------------|----------|
| 2" x 3" Rectangular Inspection Mirror | 900-103  |



## 4 Piece Pick Set

- Stainless Steel
- One Straight, One Curve, and Two Hooked Tips

| Description      | Part No. |
|------------------|----------|
| 4 Piece Pick Set | 900-205  |



## Nibbling Tool

- Cuts up to AWG 18 soft steel or 1/16" Aluminum and Plastic



| Description   | Part No. |
|---------------|----------|
| Nibbling Tool | 900-215  |

## Heat Gun



Item #: 900-119



Item #: 900-145

- Deluxe 2 temperature heat gun
- Ranges 1000°F and 600°F
- Hanging Hook

| Description             | Part No. |
|-------------------------|----------|
| Heat Gun                | 900-119  |
| 4 pc nozzle accessories | 900-145  |

## Glue Gun



Item #: 900-115

Item #: 900-118A  
Glue Sticks

| Description                | Part No. |
|----------------------------|----------|
| Glue Gun (w/o Glue Sticks) | 900-115  |
| Glue Sticks Pkg of 6       | 900-118A |

## Heat Gun Kit

**Best Value**

General purpose heat gun deliver airflow and has 1.1" diameter nozzle. Well balanced and lightweight body. Two positions switch and temperature settings at 716°F and 932°F. Double insulated with an impact resistant heating element make the heat gun ideal for industrial applications.



Motor housing

1.1"Diameter nozzle

Two positions switch and temperature settings at 716°F and 932°F

**New**



Blow molded case and 5 pcs accessories are included.

| Description | Voltage       | Watt               | Temperature        | Part No. |
|-------------|---------------|--------------------|--------------------|----------|
| Heat Gun    | 110~120V 60Hz | I-1000W / II-1600W | I-380°C / II-500°C | SS-612A  |

## 6 In 1 Mini Hammer


- The 6 in 1 mini hammer with five different interchangeable tips: two round steel, one flat brass, one flat plastic and one tinner's steel.



| Description        | Part No. |
|--------------------|----------|
| 6 In 1 Mini Hammer | 902-116  |

## Adjustable Wrenches

- Economy type
- 4, 6, and 8 inches
- Knurled adjustable screw
- Drop forged
- Insulated handles



Item #: 900-067

Item #: 900-068

Item #: 900-069

| Description                         | Part No. |
|-------------------------------------|----------|
| Adjustable Wrenches 4"              | 900-067  |
| Adjustable Wrenches 6"              | 900-068  |
| Adjustable Wrenches 8"              | 900-069  |
| Adjustable Wrenches 10" (not shown) | 900-223  |
| Adjustable Wrenches 12" (not shown) | 900-224  |

## Mini-Combination Wrench Set

- 10 pieces quality wrenches



| Description                                                                     | Part No. |
|---------------------------------------------------------------------------------|----------|
| Inch Size                                                                       | 900-070  |
| Closed end 7/16", 11/32", 3/8", 9/32", 5/16", 1/4", 16/64", 7/32", 5/32", 3/16" |          |
| Open end 3/8", 5/16", 11/32", 1/4" 9/32", 15/64" 7/32", 13/64" 3/16", 5/32"     |          |
| Metric Size                                                                     | 900-217  |
| Closed end 11, 10, 9, 8, 7, 6, 6, 5.5, 4.5, 4 mm                                |          |
| Open end 10, 9, 8, 7, 6, 5.5, 5, 4, 4, 4.5 mm                                   |          |

## Hammer

- 16 Ounce
- PVC Grip for Comfort



Item #: 900-179



Item #: 900-256

| Description                                       | Part No. |
|---------------------------------------------------|----------|
| Heavy Duty Curved-Claw Hammer w/Fiberglass Handle | 900-179  |
| Ball-Peen Hammer                                  | 900-256  |

## Multi-Stage Drill Bits (Titanium Coated)



| Description          | Spec.                     |                         |                     |                     |                                 | Part No. |
|----------------------|---------------------------|-------------------------|---------------------|---------------------|---------------------------------|----------|
|                      | No. of hole sizes per bit | Sizes range (hole dia.) | Pilot hole required | Electric drill size | Depth penetration for each step |          |
| 6 step 3/16-1/2"     | 6 in 1/16" increments     | 3/16 to 1/2"            | NO                  | 1/4" and larger     | 3/8"                            | 900-183  |
| 8 step 9/16-1"       | 8 in 1/16" increments     | 9/16 to 1"              | YES 1/2" or larger  | 1/2" and larger     | 1/8"                            | 900-184  |
| 13 step 1/8-1/2"     | 13 in 1/32" increments    | 1/8 to 1/2"             | NO                  | 1/4" and larger     | 1/8"                            | 900-185  |
| 10 step 13/16-1-3/8" | 10 in 1/16" increments    | 13/16 to 1-3/8"         | YES 1/4" or larger  | 1/2" and larger     | 1/8"                            | 900-186  |
| 9 step 1/4-3/4"      | 9 in 1/16" increments     | 1/4 to 3/4"             | NO                  | 3/8" and larger     | 1/8"                            | 900-187  |
| 12 step 3/16-7/8"    | 12 in 1/16" increments    | 3/16 to 7/8"            | NO                  | 3/8" and larger     | 1/8"                            | 900-188  |

## Automatic Center Punch



- For repetitive punching or riveting action
- Adjustable for light or heavy impact action
- Enlarged plastic handle for impact cushioning

| Description            | Part No. |
|------------------------|----------|
| Automatic Center Punch | 900-158  |

## 5 PC Miniature File Set



- 5 mini files with plastic grips
- Each file is a different style



Unit: inch

| Description             | Part No. |
|-------------------------|----------|
| 5 Pc Miniature File Set | 900-019  |

## 6 PC Hydraulic Punch Set




- with Hydraulic Piston

| Conduit      |             |
|--------------|-------------|
| Nominal Size | Actual Size |
| 1/2"         | 0.85"       |
| 3/4"         | 1.08"       |
| 1"           | 1.35"       |
| 1-1/4"       | 1.70"       |
| 1-1/2"       | 1.90"       |
| 2"           | 2.40"       |

## Spring Hook

Can grab small spring and wires. Suitable for field service.




Part No. : 902-070


Part No. : 902-073

| Description | Part No. |
|-------------|----------|
| Spring Hook | 902-070  |
|             | 902-073  |

## 5 PC Heavy Duty Needle File Set



- OAL: 7.08"
- Cut Length: 3.34"
- OD: 0.27"



Unit: inch

| Description                     | Part No. |
|---------------------------------|----------|
| 5 PC Heavy Duty Needle File Set | 900-216  |

## 4 PC Hydraulic Punch Set



- Punch and Die sets only

| Conduit      |             |
|--------------|-------------|
| Nominal Size | Actual Size |
| 2-1/2"       | 3"          |
| 3"           | 3-1/2"      |
| 3-1/2"       | 4"          |
| 4"           | 4-1/2"      |

Hydraulic Pump Available - P/N 900-010

| Description                           | Part No. |
|---------------------------------------|----------|
| 6 PC Hydraulic Punch Set (1/2" to 2") | 900-220  |

| Description                            | Part No. |
|----------------------------------------|----------|
| Punch and Die Sets only (2-1/2" to 4") | 900-221  |

## Alligator Clips

| Description                                                                               |                                                     | Boot Color   | Part No. |
|-------------------------------------------------------------------------------------------|-----------------------------------------------------|--------------|----------|
|    | Alligator Clip - Small (1.2") - 20 PC Pack          | with no boot | 902-027  |
|    |                                                     | Red          | 902-026  |
|                                                                                           |                                                     | Black        | 902-036  |
|    | Alligator Clip - Small (1.4") - 20 PC Pack          | with no boot | 902-029  |
|    |                                                     | Red          | 902-028  |
|                                                                                           |                                                     | Black        | 902-037  |
|    | 20 Amp Battery Clip (2.6") - 5 PC Pack              | with no boot | 902-033  |
|    |                                                     | Red          | 902-032  |
|                                                                                           |                                                     | Black        | 902-039  |
|    | Alligator Clip - Large Screw Type (2") - 20 PC Pack | with no boot | 902-030  |
|   | Alligator Clip - Large (2") - 10 PC Pack            | Red          | 902-031  |
|                                                                                           |                                                     | Black        | 902-038  |
|  | 30 Amp Battery Clip (3") - 5 PC Pack                | Red          | 902-034  |
|                                                                                           |                                                     | Black        | 902-040  |

## 17 PC Power Punch Kit

- Complete with 7 sets punches and dies
- Punches and dies hardened to C50-52
- Size: 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 9/32
- Will pierce up to 16 gauge steel



| Description           | Part No. |
|-----------------------|----------|
| 17 PC Power Punch Kit | 900-046  |