**Search Results**

Evaluate
- FAQ's

How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'F9LE10E-NM2'**

**Your search criteria matched only one product, shown below**

## F9LE10E-NM2

- Pass all TIA/EIA-568-B.3 performance requirements
- 100% factory inspected end face geometry in compliance with Telcordia GR-326-CORE, Issue 3
- Typical insertion loss per connection: 0.25dB
- UPC polished (55dB minimum return loss)
- Include color-specific keys with positive and negative keying features to visually and mechanically distinguish connections to prevent unauthorized mating with unlike keyed or non-keyed adapters
- Part of a complete keyed LC system that includes *Opti-Core*® Patch Cords and Pigtails, *OptiCam*® Pre-Polished Cam Connectors, *Opticom*® Fiber Adapter Panels (FAPs) and *Mini-Com*® Adapter Modules
- Factory terminated and 100% tested for insertion loss and return loss
- Insertion loss and return loss data recorded for every singlemode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

*Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact Customer Service for actual lead times.*
*Additonal keyed colors include the following: G– Violet, H– Aqua, J– Rose, K– Slate, L– Brown, P– White, Q– Charcoal, R– Lavender, S– Peach, T– Steel Blue, V– Maroon and W– Mint.*

| | |
|---|---|
| Part Number | F9LE10E-NM2 |
| RoHS Compliancy Status | RoHS directive is not applicable |
| Note | Intended for use in fixed installations which are outside the scope of RoHS. |
| Part Description | LC (keyed D- yellow) to pigtail, LSZH, singlemode duplex patch cord, 1.6mm jacketed cable (one duplex keyed LC connector on one end and pigtail on other end) – 9/125?m.. |
| Product Type | Keyed LSZH Patch Cords |
| Length (m) | 2 |
| Fiber Compatibility | 9/125um |
| Fiber Cable Size | 1.6mm |
| Fiber Cable Type | Jacketed |
| Connector 1 Type | LC Connector - Keyed E (Orange) |
| Connector 2 Type | Pigtail |
| Flammability Rating | LSZH (Low Smoke Zero Halogen) |
| Key Type and Color | Keyed E - Orange |
| Pricing Description | Keyed LC (E-Orange) pigtails, SM, Duplex, LSZH, 2M |
| Min. Order UOM | PC |
| Min. Order Qty. | 1 |
| BOM Qty. (# of Pkgs.) | 0 |
| Add to Favorite Product List | e |

**Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.**


Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy