Search Results

Evaluate
- FAQ's
Design a Solution
- Part Drawings
- PDF Fiber Optic..
How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'FXLD2-3M3'**

Your search criteria matched only one product, shown below

FXLD2-3M3

- Patch cords are tested to support network transmission speeds up to 10 Gb/s for link lengths up to 300 meters with an 850nm source per IEEE 802.3ae 10 GbE standard
- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Backward compatible for use with all 50/125 ?m system requirements
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- SC Duplex Patch Cords include SC Duplex Clips to maintain polarity
- Highest quality flame retardant fiber optic cable with tight -buffered coating on each optical fiber

Additional lengths and availability: Patch cords are available in 1 – 10 meter lengths in 1 meter increments, and 15, 20, 25 and 30 meter lengths. Pigtails are available in 1, 2, and 3 meter lengths. Ex: To order lengths other than 1 meter, replace the 1 after the M (FXE10-10M1Y) with the desired length (FXE10-10M2Y for 2 meter length). The above lengths are stock items. For other lengths, contact Customer Service for actual lead times.

Part Number	FXLD2-3M3
RoHS Compliancy Status	RoHS directive is not applicable
Note	Intended for use in fixed installations which are outside the scope of RoHS
Part Description	ST to SC multimode duplex patch cord, 3mm jacketed cable (two ST connectors on one end and one duplex SC connector on the other end)– 10Gig™ 50/125 ?m.
Product Type	Hybrid Patch Cords
Length (m)	3
Fiber Compatibility	10 GbE 50/125?m
Fiber Cable Size	3mm
Fiber Cable Type	Jacketed
Fiber Type	Multimode
Cable Color	Aqua
Cable Type	Duplex
CE Compliant	No
Connector 1 Type	ST Connector
Connector 2 Type	SC Connector
End Configurations	ST to SC
Fiber Count	2
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Pricing Description	ST-SC LSZH 10 GbE 50?dupl 1.6mm Patch Cord 3m
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy