

- Replacement for 27W PAR16 halogen lamp
- Up to 85% energy saving
- Lifetime of 30,000 hrs
- Suitable replacement for halogen or incandescent spots. Perfectly highlights the corridors, stairwells, bathroom etc at home and in hospitality areas.



Order Code 52137

General Data

Lamp Socket GU10
Design Lens

Geometric Data

Length (mm) 57.2
Diameter (mm) 50
Weight (g) 54

Electric Data

Wattage (W) 4.0
Wattage Equivalent (W) 27
Voltage (V) 220-240
Power Factor >0.40
Operating Frequency (Hz) 50-60

Photometric Data

Luminous Flux (lm) 200
Luminous Flux 90° (lm) 160
CRI ≥ 80
CCT (K) 3000
Luminous Intensity (cd) 750
Beam Angle (°) 20



Lifespan

Lifetime (hrs) 30,000
Switching Cycle 20,000

Dimmability No

Energy Efficiency Class A





Order Code 52137

Product Description LED PAR16 GU10 4.0W 3000K WW 160LM 20DEG

Technical Packaging Details

Barcode	023942521372
EAN 128	(02)00023942521372(37)04(91)204
EAN 14	50023942521377
Pack Dimensions (HxWxL)	130 mm x 103 mm x 51 mm
Pack Weight	TBC
Carton Qty (Shipping Unit)	4
Carton Dimensions (HxWxL)	160 mm x 117 mm x 223 mm
Cartons/Pallet	150
Layers/Pallet	5
Units/Pallet	600

Photometric Diagram

52137

