米国軍用規格長蝶番(MS規格)

MILITARY STANDARD CONTINUOUS HINGES

MS-20257・MS-35822・MS-35823・MS-35825

アルミニウム製

輸入品　ステンレス

特　徴　Feature

- アルミ製で耐食性・耐薬品性に優れています。
- 切断して使用できます。

- Corrosion-resistant/chemical-resistant aluminum is used.
- Cut and use.

仕　様
- 材　　質：アルミニウム合金板(軸はステンレス製)
- 表面仕上：アルマイト処理

用　途
- 航空機・通信機器・測定機器・船舶・車両・小型コンテナなどの筐体

納　期
- 標準品・・・納期お問合せください

備　考
- 表中の　　は中止予定品です。納期お問合せください。
- 輸入品のため色が異なることがあります。
- 航空機にはMS規格品をご使用ください。
- ⚠ 必要な寸法に切断後軸にカシメ等の抜け止め加工をしてご使用ください。
- 両端に抜け止め加工を行う場合は、必ず同じ羽根で行ってください。異なる羽根で行うと作動不良の原因となります。
- 長尺商品のため、送料が掛かります。詳細はお問合せください。

Specifications
- Aluminum alloy plate. (Shaft: Stainless steel)
- Finish: Alumite treatment

Specific-use
- Cases for aircraft, communication equipment, measuring equipment, ships, vehicles and small containers

Remarks
- The gray shading on the chart indicates items scheduled to be discontinued. Please inquire regarding delivery dates.
- A color is sometimes different for the imports.
- The MS (Military Standard) articles must be used for the air crafts.
- ⚠ The hinge is not processed to prevent extraction of the shaft. After cutting the hinge to size and before use, fix stops, etc., on the shaft to prevent its extraction.
- When fixing stops on both ends, always fix on the same wing. Fixing on different wings may cause faulty operation.







商品番号 Product No.	RoHS	CAD	L1	L2	W	t	φD	製品質量(g) Mass	コード Code	単　価 Price	量販価格 Bulk Price 数量 Quantity	単価 Price
MS-35822-9A			1829	12.4	27	1.0	2.3	180	12463	価格はお問合せください		
MS-35822-10A			1829	12.4	32	1.0	2.3	210	12464			
MS-35822-12A			1829	12.4	51	1.0	2.3	320	12466			
MS-35823-6A			1829	16	38	1.2	3.2	320	12467			
MS-35825-14A			2133	25	38	1.5	3.2	480	12469			
MS-35825-16A			2133	25	64	1.5	3.2	690	12471			

軸はステンレス製です。　Shaft is made of stainless steel　　※大量のご注文は更にお安くなります。

●：RoHS指令対応品　▲：RoHS指令に対応可能です。

商品番号 Product No.	RoHS	CAD	L1	L2	W	t	φD	製品質量(g) Mass	コード Code	単　価 Price	量販価格 Bulk Price 数量 Quantity	単価 Price
MS-20257-P1			72(1829)	½(12.7)	¾(19.1)	0.032(0.8)	0.062(1.6)	120	12457	価格はお問合せください		
MS-20257-P2			72(1829)	½(12.7)	1 1/16(27.0)	0.040(1.0)	0.089(2.3)	245	12458			
MS-20257-P3			72(1829)	½(12.7)	1¼(31.8)	0.040(1.0)	0.089(2.3)	220	12459			
MS-20257-P4			72(1829)	½(12.7)	1½(38.1)	0.040(1.0)	0.089(2.3)	270	12460			
MS-20257-P6			72(1829)	2 (50.8)	2 (50.8)	0.064(1.6)	0.179(4.5)	700	12462			

単位はインチ・( )内寸法はmmを示します。　Unit: inches/dimensions in parentheses: mm　　※大量のご注文は更にお安くなります。

※表中の　　は中止予定品です。　The gray shading on the chart indicates items scheduled to be discontinued.

●：RoHS指令対応品　▲：RoHS指令に対応可能です。