Product data sheet
Characteristics

QO225
MINIATURE CIRCUIT BREAKER 120/240V 25A

Product availability: Stock - Normally stocked in distribution facility

Price*: 67.00 USD

Main

Commercial Status	Commercialised
Product or component type	Miniature Circuit Breaker
Range of product	QO
[In] rated current	25 A
Product certifications	CSA UL listed
[Ue] rated operational voltage	120/240 V AC
Mounting mode	Plug-in
Poles description	2P
Short-circuit current	10 kA
Number of spaces required	2
Circuit breaker type	Standard
Circuit breaker application	HACR rated
Electrical connection	Pressure plate
AWG gauge	14...8 AWG aluminium 14...8 AWG copper
Accessory / separate part type	None

Ordering and shipping details

Category	00004 - QO,QOT 10-30A 1P;10-60A 2P
Discount Schedule	DE2A
GTIN	00785901012412
Nbr. of units in pkg.	5
Package weight(Lbs)	0.54
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will be Compliant on 3Q2014
REACh	Reference not containing SVHC above the threshold

Contractual warranty

Period	18 months

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative