

Isobar Surge Suppressor - Premium surge, spike and line noise protection

MODEL NUMBER: **EURO-4**



Description

For more than 20 years, America's leading companies have trusted Tripp Lite's Isobar Premium surge and noise suppressors to protect sensitive computer, networking and telecom equipment. With more than 18 million satisfied customers, the Isobar remains the world's #1 selling premium surge suppressor. Loaded with a generous combination of high quality components, near indestructible all-metal case and unique noise filtration system, the isobar offers the highest level of protection attainable in a multi-outlet strip. Robust surge suppression circuits with sine-wave tracking offer extreme levels of protection against the heaviest surge conditions exceeding IEEE 587 category A & B specifications. Isobar's unique protection system combines large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and multiple layers of metal oxide varistors into exclusive isolated filter banks that remove EMI/RFI interference, even noise generated by other pieces of connected equipment. EURO-4 offers 4 outlets arranged in two filter banks to prevent system crashes, reboots and performance problems common as noisy system peripherals are powered off and on. Surge suppression rated at 680 joules offers network-grade protection. Widely spaced IEC320-C13 outlets accommodate up to 2 large transformer plugs without blocking outlets. Detachable IEC-320 C14 inlet connection accepts a variety of detachable cordsets to match country or site-specific wall receptacles. Two-meter C13 to C14 interconnection cable and keyhole mounting tabs included. PLUG/OUTLETS: Input: IEC320 C14 inlet/Output: 4 IEC320 C13 outlets/2m C13 to C14 interconnection cable included ELECTRICAL: 200-240V AC, 50/60Hz (Use at 120V supported) SUPPRESSION: AC: 300V RMS Clamping/680 joules FORMAT: Corded all-metal strip with transformer spaced outlets

Features

- Tripp Lite's ISOBAR is the world's #1 selling premium suppressor series with more than 18 million satisfied customers and a safety-tested history of 20+ years
- Robust surge suppression with sine-wave tracking protects against the heaviest of surge conditions, exceeding IEEE category A&B specifications
- Multi-component suppression circuits combine toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and multiple layers of metal oxide varistors into exclusive isolated filter banks that remove EMI/RFI interference, even noise from other pieces of connected equipment.
- 4 outlets arranged in two filter banks prevent system crashes, reboots and performance problems common as noisy peripherals are powered off and on.
- Network grade surge suppression rated at 680 joules
- Widely spaced outlets accommodate up to 2 large transformer plugs without blocking outlets
- Lighted power switch confirms power on/off status

Highlights

- 4 outlets/2 m cord
- 680 joule rating
- All metal housing with LEDs
- Isolated filter banks

Applications

- Ideal for premium protection of personal computers with peripherals, network and CAD/CAM/CAE workstations, internetworking accessories, telecommunications systems, point of sale equipment, audio/video and home theater systems in any home, office or industrial application.

Package Includes

- EURO-4 premium surge suppressor
- Instruction manual with warranty information



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- 2m C13 to C14 interconnection cable included
- Keyhole mounting tabs for installation in a wide variety of applications
- 200-240VAC, 50/60Hz electrical compatibility

Specifications

OVERVIEW	
Intended Application	Home/Office, Computer Networks
OUTPUT	
Frequency compatibility	50 / 60 Hz
Circuit Breaker (amps)	9
Outlet quantity / type	4 IEC-C13
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Input connection type	IEC-C14 inlet connection accepts a variety of detachable cord sets to match country or site-specific wall receptacles
Input plug features	Includes 1 detachable IEC-320 C13 to C14 cable
Input cord length (ft.)	6.6
Input cord length (m)	2
Voltage compatibility (VAC)	220-250
Maximum Surge Amps	15000
UPC ASSIGNMENT	
Unit Carton UPC#	037332010049
LEDS ALARMS & SWITCHES	
Switches	Two position orange illuminated on/off power switch
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	680
AC suppression response time	NM = 0 ns. CM = <1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	300
AC suppression components used	Metal oxide varistors, toroidal balanced chokes, ferrite rod-core inductors and VHF capacitors.
Isolated filter banks	Unique isolated filter bank design offers additional filtering between each pair of outlets on the strip to prevent electrical noise interference between connected loads. Includes 2 filter banks.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Immunity	Conforms to IEE 587 / ANSI C62.41
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Unit Dimensions (HWD/in)	3.5 x 7 x 2.5
Unit Dimensions (HWD/cm)	8.9 x 17.8 x 6.4
Material of construction	Metal
Integrated keyhole mounting tabs	Metal end caps are fitted with keyhole mounting tabs for wallmount installation
Housing Color	Light Gray
Receptacle Color	Black
AC line cord color	Light Gray
Style	Strip
Outlets center to center measurement	Distance between horizontal outlets = 53mm; Distance between vertical outlets = 38.10mm
Keyhole slot center to center measurement	Distance between horizont tabs = 162.13mm; Distance between vertical tabs = 58.17mm
SPECIAL FEATURES	
Appearance	Rugged all-metal strip format with high quality snap-in receptacles and detachable line cord
Right-Angle Plug	Yes
CERTIFICATIONS	
Approvals	CE
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[EURO-4](#)