CB4200 Series Supplemental Circuit Breakers

Circuit Breakers
Thermal Magnetic Type

- Rated from 0.05 to 16.0 amps
- Available in single or double pole configurations
- Features a tease free design to reduce contact damage
- Offers push button trip/reset function
- Trip free design means the breaker cannot be held closed against a fault
- Mounts on 32mm* or 35mm DIN-rail
- UL 1077 recognized

CB4200 Series
Single Pole

CB4200 Series
Double Pole

Ordering Data	Type: Single Pole		Type: Double Pole	
	Current Ratings (amps)	Part No. TS 35 *For TS 32 Rail, see adapter below	Current Ratings (amps)	Part No. TS 35 *For TS 32 Rail, see adapter below
	0.05	**9124083500**	0.05	**9124223500**
	0.08	**9124653500**	0.08	**9124233500**
	0.1	**9104173500**	0.1	**9120353500**
	0.2	**9104183500**	0.2	**9124243500**
	0.3	**9129813500**	0.3	**9124263500**
	0.4	**9124093500**	0.4	**9124273500**
	0.5	**9101003500**	0.5	**9129583500**
	0.6	**9124113500**	0.6	**9124283500**
	0.7	**9129563500**	0.7	**9124293500**
	0.8	**9101103500**	0.8	**9129593500**
	1.0	**9101203500**	1.0	**9129613500**
	1.2	**9101303500**	1.2	**9129623500**
	1.3	**9124123500**	1.3	**9124313500**
	1.4	**9124133500**	1.4	**9124323500**
	1.5	**9101403500**	1.5	**9129633500**
	1.8	**9124143500**	1.8	**9124333500**
	2.0	**9101503500**	2.0	**9129643500**
	2.5	**9101603500**	2.5	**9129653500**
	3.0	**9101703500**	3.0	**9129663500**
	3.5	**9124163500**	3.5	**9124343500**
	4.0	**9104353500**	4.0	**9129713500**
	4.5	**9124173500**	4.5	**9124353500**
	5.0	**9101803500**	5.0	**9129673500**
	5.5	**9107833500**	5.5	**9124363500**
	6.0	**9103813500**	6.0	**9124373500**
	6.5	**9120043500**	6.5	**9124383500**
	7.0	**9104153500**	7.0	**9124393500**
	8.0	**9103003500**	8.0	**9104673500**
	9.0	**9104613500**	9.0	**9124423500**
	10.0	**9101903500**	10.0	**9129683500**
	11.0	**9124183500**	11.0	**9124433500**
	12.0	**9107843500**	12.0	**9124443500**
	13.0	**9124193500**	13.0	**9124453500**
	14.0	**9107853500**	14.0	**9124463500**
	15.0	**9102003500**	15.0	**9129693500**
	16.0	**9124213500**	16.0	**9124473500**

Trip Curves
Thermal Magnetic Type
Typical time/current characteristics at 23ºC

CB4200 Series

M1+ 0.05 to 7.5 A



M1+ 8 to 16 A



***Adapter foot – dimensions in mm (in.)**



9102100000
TS32 adapter