



REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1272	D	Renamed...was Nccb-*	JWM	12/19/01	DJC	12/28/01	DJC	12/28/01
1865	E	RoHS ADDED	DCM	10/17/05	JWM	10/18/05	JWM	10/18/05



PART #	"D" HOLDING DIA.	"E" REF.
NCCB-3	3/16 (4.8)	25/64 (9.9)
NCCB-4	1/4 (6.4)	27/64 (10.7)
NCCB-6	3/8 (9.5)	31/64 (12.3)

NOTES:

1. MATERIAL: NYLON 6/6
2. COLOR: NATURAL
3. FLAMMABILITY RATING: UL94V-2
4. CONTINUOUS USE TEMPERATURE:
-40°F(-40°C) TO 167°F(75°C)

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
Tolerances: Unless
Otherwise Specified:
.XX = ±.010
.XXX = ±.005
Fractional = ±1/64
Angles = ±1°

DRAWN BY:
J.A.P.
CHECKED BY:
JOHN COLE
APPROVED BY:
K.M.

DATE:
12/5/94
DATE:
12/05/94
DATE:
12/7/94

DRAWING TITLE:
"N" Series Cable Clamps

SIZE A	DWG. NO. TA-474	ELECTRONIC FILE TA-474.dwg	REV E
SCALE: NTS		U.O.M.: INCHES [mm]	SHEET: 1 OF 1