THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST
AF	50

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	N	REVISED PER ECR-13-004343	30JUL13	KH	KR



1 MATES WITH .032±.001x.110 OR .125 TAB

2 WIRE STRIP LENGTH .281

3 INSULATION SIZE .120 MAX DIA

4 CONTINUOUS STRIP ON REELS

5 DIMENSION DOES NOT INCLUDE TRIM BURR

6 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA

MATERIAL & FINISH	PART NO
HOUSING:NYLON,COLOR-BLACK TRANSLUCENT RECEPTACLE:BRASS TIN	9-520272-2
HOUSING:NYLON,COLOR-RED TRANSLUCENT RECEPTACLE:BRASS TIN	2-520272-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± .015
4 PLC	± -
ANGLES	± -

MATERIAL: SEE TABLE

FINISH: SEE TABLE

DWN P FORTNEY 11/9/88
CHK MS FEHER 11/9/88
APVD K RANDOLPH 11/11/88
PRODUCT SPEC 108-2043
APPLICATION SPEC 114-2123
WEIGHT -

TE Connectivity

NAME: RECEPTACLE ASSY,ULTRA-FAST, .110/.125 SERIES, 22-18AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-520272	-

CUSTOMER DRAWING

SCALE	SHEET	REV
5:1	1 OF 1	N