THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST
AF	50

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	S	REVISED PER ECR-13-004343	30JUL13	KH	KR

1 MATES WITH .032±.001x.250 TAB

2 WIRE STRIP LENGTH .281

3 INSULATION SIZE .160 MAX DIA

5 DIMENSION DOES NOT INCLUDE TRIM BURR

6 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA



HOUSING:NYLON,COLOR-BLUE TRANSLUCENT RECEPTACLE: BRASS TIN	3-350820-2
MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± .015
4 PLC	± -
ANGLES	± -

MATERIAL: SEE TABLE

FINISH: SEE TABLE

DWN P FORTNEY 10/5/88
CHK JR RUTH 10/6/88
APVD KA RANDOLPH 10/6/88
PRODUCT SPEC 108-2043
APPLICATION SPEC 114-2123
WEIGHT -

TE Connectivity

NAME: RECEPTACLE ASSY,ULTRA-FAST, LOOSE PIECE,.250 SERIES,16-14 AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-350820	-

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV S