Search Results

Evaluate
- FAQ's
- Technical Papers
  - DOCMTechnical Da..
  - PDFTechnical Da..

Design a Solution
- Part Drawings
  - PDFC240X240A*T- ..
- Specification Sheets
  - PDFRaised Panel..

How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'C240X240A0T-30'**

Your search criteria matched only one product, shown below

C240X240A0T30

- Raised thermal transfer printable surface with high -tack adhesive for strong holding power
- Variety of sizes and colors for a wide range of applications
- Thermal transfer print technology provides crisp, clear, and durable text
- Use with Panduit thermal transfer resin ribbons

Part Number	C240X240A0T-30
RoHS Compliancy Status	Compliant
Part Description	Black, raised panel push button label.
Color	Black
Height (In.)	2.40
Height (mm)	60.9
Width (In.)	2.40
Width (mm)	60.9
Hole Diameter (In.)	1.18
Hole Diameter (mm)	30.0
Pricing Description	Raised Panel Label, Keyhole, 2.4"W x 2.4"H (61.0mm x 61.0mm), Black
Print-On Area Height (In.)	0.90
Print-On Area Height (mm)	22.9
Min. Order UOM	PC
Min. Order Qty.	500
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy