FIBOX CAB CAB PC 504020 T3B

Sample photo

Order symbol: CAB PC 504020 T3B
Product nbr: 8113062

Description: Cabinet, PC
Remarks: Locks on the long side

EAN: 6418074020376
El. number:

Finland	3424174
Denmark	8212019276
Italy	7822060
Sweden	2539955

Including: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:

	L	W	H
mm:	500	400	200
inch:	19.7	15.7	7.9

Materials:

Material:	PC
Base colour:	RAL 7035
Cover colour:	Smoked grey
Gasket material:	EPDM

Temperatures:

Short term:	-40 … 120 °C
Continuous:	-40 … 80 °C
Short term:	-40 … 250 °F
Continuous:	-40 … 175 °F

Accessories:

EKIV 54	Mounting plate
EKIV 37	DIN-35 Mounting rail
EKIV 47	DIN-35 Mounting rail
FP A 54	Swing-out door, aluminium
FP 54	Front plate
FP 18X2-54	Front Plate
DRF 54	DIN rail frame set

Rating:

Ingress Protection (EN 60529): IP 65
Impact Resistance (EN 50102): IK 08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
UV resistance: UL 508
Flammability Rating (UL 746 C 5): UL 94 5V
Glow Wire Test (IEC 695-2-1) °C: 960
UL Type: UL TYPE 1, 4, 4X, 12, 13

Certificates:

Germanischer Lloyd (GL)
Underwriters Laboratories
Fimko
Lloyds Register of Shipping (LR)
Europe EN 50298 1998
UL Canada
Gost R



(c) Fibox OY, Data subject to change without notice