

TOLERANCE = ±.010

COIL: @ 25°C

RESISTANCE	300 OHMS ± 10%
NOMINAL VOLTAGE	28.0 VDC
MUST OPERATE	13.0 VDC
MUST RELEASE	7.0 VDC MAX, 1.6 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 50 g's 11 MS. DURATION

TEMPERATURE -70 °C TO +125 °C

NOTES: OPERATE & RELEASE 10 MS MAX.
OPERATE BOUNCE 2 MS MAX.
RELEASE BOUNCE 5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: 10 AMPS 28 VDC, 10 AMPS 115 VAC 400 HZ RESISTIVE 100,000 OPERATIONS

DR. R.B. 9/14/98 CK. 9/14/98

COMMUNICATIONS INSTRUMENTS, INC.

CUST. QPL
CUST. NO. MS27245-1

TYPE "07" RELAY

B07D112BC4-0007