


FEATURES


- Standard 7.0mm x 5.0mm 4-Pad Surface Mount Package
- HCMOS/TTL Compatible Output
- Fundamental and 3rd Overtone Crystal Designs
- Frequency Range 1 – 200 MHz
- Frequency Stability ± 50 ppm Standard, ± 25 ppm and ± 20 ppm Available
- Operating Voltages +5.0Vdc or +3.3Vdc
- Operating Temperature to -40°C to +85°C
- Output Enable Standard
- Tape & Reel Packaging
- **RoHS/Green Compliant (6/6)**



APPLICATIONS

Applications for Model CB3 and CB3LV include digital video, networking equipment, wireless communications, broadband access, Ethernet/Gigabit Ethernet, microprocessors/DSP/FPGA, storage area networks, fiber channel, computers and peripherals, test and measurement, SONET/SDH/DWDM, base stations and Pico cells.

ORDERING INFORMATION



1] 6I Stability/Temperature combination is not available.

2] These stabilities are not recommended for new designs.

3] Frequency is recorded with only leading significant digits before the 'M' and 4 - 6 significant digits after the 'M' (including zeros).

[Ex. 3.579545 MHz, code as 3M579545; 14.31818 MHz, code as 14M31818; 125 MHz, code as 125M0000]

4] CTS Distributors may add a -T or -1 at the end of the part number to indicate Tape and Reel packaging.

**Not all performance combinations and frequencies may be available.
Contact your local CTS Representative or CTS Customer Service for availability.**

PACKAGING INFORMATION [reference]

Device quantity is 1,000 pieces maximum per reel.



ELECTRICAL CHARACTERISTICS

ELECTRICAL PARAMETERS	PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
	Maximum Supply Voltage	V_{CC}	-	-0.5	-	+7.0	V
	Storage Temperature	T_{STG}	-	-40	-	+100	°C
	Frequency Range						
	CB3	f_0	-	1.5	-	107	MHz
	CB3LV		-	1.5	-	200	
	Frequency Stability	$\Delta f/f_0$	See Note 1 and Ordering Information	-	-	20,25,50 or 100	± ppm
	Aging	Δf	First year	-	3	5	± ppm
	Operating Temperature						
	Commercial	T_A	-	-20	25	+70	°C
	Industrial			-40		+85	
	Supply Voltage						
	CB3	V_{CC}	±10%	4.5	5.0	5.5	V
	CB3LV			3.0	3.3	3.6	
	Supply Current		Frequency Range				
	CB3	I_{CC}	Tested load condition noted for typical values. 1.5MHz to 20MHz $C_L=50pF$	-	10	25	mA
			20.001MHz to 80MHz $C_L=50pF$	-	30	50	
			80.001MHz to 107MHz $C_L=15pF$	-	40	80	
	CB3LV		1.5MHz to 20MHz $C_L=15pF$	-	7	12	
			20.001MHz to 80MHz $C_L=15pF$	-	20	40	
			80.001MHz to 200MHz $C_L=15pF$	-	30	60	
	Output Load	C_L	1.5MHz to 50MHz 50.001MHz to 80MHz 80.001MHz to 200MHz	- - -	- - -	50 30 15	pF
	Output Voltage Levels						
	Logic '1' Level	V_{OH}	CMOS Load 10 TTL LOAD	90% V_{CC} $V_{CC}-0.6V$	-	-	V
	Logic '0' Level	V_{OL}	CMOS TTL Load	-	-	10% V_{CC} 0.4	
	Output Current						
	Logic '1' Level	I_{OH}	$V_{OH} = 3.9V/2.2V$ $V_{CC} = 4.5V/3.0V$	-	-	-16/-8	mA
	Logic '0' Level	I_{OL}	$V_{OL} = 0.4V$ $V_{CC} = 4.5V/3.0V$	-	-	+16/+8	
	Output Duty Cycle	SYM	@ 50% Level	45	-	55	%
	Rise and Fall Time		@ 10% - 90% Levels				
	CB3	T_R, T_F	Tested load condition noted for typical values. 1.5MHz to 20MHz $C_L=50pF$	-	8	10	ns
			20.001MHz to 80MHz $C_L=50pF$	-	5	8	
			80.001MHz to 200MHz $C_L=15pF$	-	2.5	5	
	CB3LV		1.5MHz to 20MHz $C_L=15pF$	-	6	8	
			20.001MHz to 80MHz $C_L=15pF$	-	3	5	
			80.001MHz to 200MHz $C_L=15pF$	-	1.5	3	
	Start Up Time	T_S	Application of V_{CC}	-	-	10	ms
	Enable Function						
	Enable Input Voltage	V_{IH}	Pin 1 Logic '1', Output Enabled	2.0	-	-	V
	Disable Input Voltage	V_{IL}	Pin 1 Logic '0', Output Disabled	-	-	0.8	
	Enable Time	T_{PLZ}	Pin 1 Logic '1'	-	-	200	ns
	Standby Current	I_{ST}	Pin 1 Logic '0', Output Disabled	-	-	10	µA
	Period Jitter, Pk-Pk	-	-	-	-	50	ps
	Period Jitter, RMS	-	-	-	-	5	
	Phase Jitter, RMS	-	Bandwidth 12kHz - 20MHz	-	-	1	

Notes:


1. Inclusive of initial tolerance at time of shipment, changes in supply voltage, load, temperature and 1st year aging.

ELECTRICAL CHARACTERISTICS

LVC MOS OUTPUT WAVEFORM



TEST CIRCUIT, CMOS LOAD



ENABLE TRUTH TABLE


PIN 1	PIN 3
Logic '1'	Output
Open	Output
Logic '0'	High Imp.

D.U.T. PIN ASSIGNMENTS

PIN	SYMBOL	DESCRIPTION
1	EOH	Enable
2	GND	Circuit & Package Ground
3	Output	RF Output
4	V _{CC}	Supply Voltage

MECHANICAL SPECIFICATIONS

PACKAGE DRAWING



MARKING INFORMATION

- ** – Manufacturing Site Code.
[Note a dash may follow the site code and is acceptable.]
- XXMXXXXXX – Frequency is marked with only leading significant digits before the 'M' and 4 – 6 digits after the 'M' (including zeros).
Ex. XMXXXXXX [3M579545]
XXMXXXXXX [14M31818]
XXMXXXXXX [125M0000]
- YYWW – Date code, YY – year, WW – week.
- ST – Frequency stability/temperature code.
[Refer to Ordering Information.]
- V – Voltage code. 3 = 3.3V, 5 = 5.0V.

NOTES

- Termination pads [e4]. Barrier-plating is nickel [Ni] with gold [Au] flash plate.
- Reflow conditions per JEDEC J-STD-020, 260°C maximum.
- Moisture Sensitivity Level 1 per JEDEC J-STD-020.

SUGGESTED SOLDER PAD GEOMETRY

C_{BYPASS} should be ≥ 0.01 uF.

