CATALOG

Cross Reference
- Competitive Products
- Military Spec P/Ns
- Tyco Brand P/Ns

- Part Number Search
- Document Search
- Product Type Search
- Product Family Search
- Alphabetical Search
- RoHS/ELV Compliance & Alternates
- CAD Model Search
- Brand Search
- Tool Search
- Multiple Part Comparison
- Lead Free Solutions
- Help/Glossary

Home

e-bulletin newsletter
SUBSCRIBE NOW!
click here

Timer Products
↳ Timer Contacts

AMP **928924-1** ✔ Active

Directive 2002/95/EC Compliant RoHS Compliant

Product Feature Selector

Photographs & Line Drawings

Line Drawing

(The photographs and/or line drawings are representative images of a product, for viewing purposes only.)

Product Documentation & Related Product Information

Product Drawings:
- 2.8mm F.F. Tab (PDF, German)

Catalog Pages/Data Sheets:
- Automachine and General Products (PDF, English)

Application & Product Specifications/Instruction Sheets:
- None Available

CAD Files:
- None Available

List all Documents

Related Product Information:
- Tooling
- Pricing & Availability
- Product Line Information
- Sales Information

Product Features
Please use the Product Drawing for all design activity

RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Not relevant for lead free process
Product Type:	Contact
Contact Type:	Junior Timer, Junior-Power-Timer
Gender:	Tab
Wire Range (mm [AWG]):	1.50-3.0²
Insulation Diameter (mm [in]):	2.29 – 3.51 [0.090 – 0.138]
Single Wire Sealing System:	No
Contact Material:	CuZn30
Tab Type:	Asymmetric Cantilever Steel Spring
Tab Fit (mm [in]):	2.79 x 0.81 [.110 x .032]
Contact Mating Area Plating:	Tin
Terminate To:	Wire
Packaging Method:	Loose Piece
GET 0.64 Connector System:	No
Brand:	AMP

Additional Features

RoHS/ELV Compliance History:	Always was RoHS compliant
Insulation Type:	FLR
Cantilever Spring Material:	Stainless Steel
Comment:	For RB-Wires.

Copyright and Privacy Statement
Visit Tyco International Ltd.