



Sample photo

Order symbol: PCM 150/150 G
Product nbr: 6016317
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074052230
El. number:
 Finland 3435218
 Denmark 8212027501
 Sweden 2535334

Including: Base with metric knock-outs and TPE gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:				Rating:
L	W	H		
mm:	180	130	150	Ingress Protection (EN 60529): IP 66/67
inch:	7.1	5.1	5.9	Impact Resistance (EN 50102): IK 08
Materials:				Electrical insulation: Totally insulated
Material:	PC			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035			UV resistance: UL 508
Cover colour:	RAL 7035			Flammability Rating (UL 746 C 5): UL 94 5V
Cover screws material:	Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:	Grey			NEMA Class: NEMA 1, 4, 4X, 6
Gasket material:	TPE			
Temperatures:				Certificates:
Short term:	-40 ... 120 °C			Germanischer Lloyd (GL)
Continuous:	-40 ... 80 °C			Underwriters Laboratories
Short term:	-40 ... 250 °F			Det Norske Veritas
Continuous:	-40 ... 175 °F			Fimko
Accessories:				Europe EN 50298 1998
MIV 150	Mounting plate			UL Canada
MIN 10	DIN-15 Mounting rail			Gost R
MIN 15	DIN-15 Mounting rail			
MIV 10	DIN-35 Mounting rail			
MIV 15	DIN-35 Mounting rail			
FP A 150/180	Front plate			
HFP 180	Front plate hinge series			

