



Sample photo

Order symbol: ABS 100/100 LG
Product nbr: 6082304
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074022790
El. number:
Finland: 3420507
Denmark: 8212023123
Italy: 7361020
Sweden: 2535709
Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		130	80	100	Ingress Protection (EN 60529): IP 66/67
inch:		5.1	3.1	3.9	Impact Resistance (EN 62262): IK 07
Materials:					Electrical insulation: Totally insulated
Material:		ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 650
Cover screws material:		Polyamide			NEMA Class: NEMA 1, 4, 4X, 6
Cover screws colour:		Grey			
Gasket material:		TPE			
Temperatures:					Certificates:
Short term:		-40 ... 80 °C			Fimko
Continuous:		-40 ... 60 °C			Europe EN 62208: 2003
Short term:		-40 ... 175 °F			Gost R
Continuous:		-40 ... 140 °F			
Accessories:					
MIV 100		Mounting plate (Galvanized steel)			
MIN 5		DIN-15 Mounting rail			
MIN 10		DIN-15 Mounting rail			
MIV 5		DIN-35 Mounting rail			
MIV 10		DIN-35 Mounting rail			
FP A 100/130		Front plate (Aluminium)			
HFP 130		Front plate hinge series (2 pcs)			
FP 22046		Wall fastening lug (4 pcs)			

