FO-50360-L

HONEYWELL PART NUMBER
V15H16-CZ100A05-K
PRODUCT CODE
CFW2048

REV	DOCUMENT	CHANGED BY	CHECK
A	0038670	VS 10APR08	BLR







NOTES:

1. TERMINALS WILL ACCEPT 6.35mm WIDE QUICK CONNECT RECEPTACLES AND COMPLY WITH EN61058-1 REQUIREMENTS.

CHARACTERISTICS	
OPERATING FORCE:	120gf MAX.
DIFFERENTIAL FORCE:	
RELEASE FORCE:	20gf MIN.
FREE POSITION:	
OPERATING POSITION:	20.6±0.8MM.
PRE-TRAVEL:	1.6MM MAX.
DIFFERENTIAL TRAVEL:	0.4MM MAX.
OVER-TRAVEL:	0.8MM MIN.
FULL OVERTRAVEL FORCE:	

ELECTRICAL DATA

CONTACT ARRANGEMENT
S.P.D.T

16(4)A 250V~
25T150 µ 5E4

16A 1/2HP 125/250VAC

DESIGN UNITS: MM
TOLERANCES UNLESS NOTED:

NO PLACE	X	±	±
ONE PLACE	.X	±	±
TWO PLACE	.XX	±	± 0.40
THREE PLACE	.XXX	±	±
ANGLES	X	±	± 2°

THIRD ANGLE PROJECTION

DRAWN	KSR	01APR08
CHECK	RJ	01APR08

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY

AutoCAD

Honeywell

TITLE
SWITCH - BASIC

SIZE	TYPE	CAGE CODE	DRAWING NAME	REV
B	I		V15H16-CZ100A05-K	A

SCALE NTS SHEET 1 OF 1