

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,1998.

© COPYRIGHT 1998 By Tyco Electronics Japan G.K.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD

J

REVISED PER ECR-12-011159

27JUN12

B.P

F.M

—*; AS SHOWN

21.6 MAX
最大

0.5 MAX
最大

6

0.5 MAX
最大

TRADE MARK

トレードマーク

0.5厚タブと嵌合
MATE WITH
0.5mm THK TAB

5.6

A-A

3

(3.2)

B-B

4.6

(4.5)

C-C

A

B

C

1.7

3.2

A

B

C

1 適用ハウジング型番
172074, 172075

1 APPLICABLE HOUSING P/N
172074, 172075

2 PARTS 170325-7 & 170331-7 WERE APPLIED
NYE LUBE.

170331-7	170325-1	170325-7
—H—	錫めっき済高耐熱銅合金 0.3t PRE-TIN HIGH HEAT RESISTANCE COPPER ALLOY 0.3t THK	170325-6
—H—	錫めっき済 りん青銅 0.3t PRE-TIN PHOS BRO 0.3t THK	170325-5
OBSOLETE	170331-2	170325-2
	ニッケルめっき仕上 りん青銅 0.3t PHOS BRO 0.3t THK NICKEL PL	
	170331-1	170325-1
	錫めっき済黄銅 0.3t PRE-TIN BRASS 0.3t THK	
ばら状端子型番 LOOSE PIECE P/N	材料 MATERIAL	型番 STRIP FORM P/N
WIRE RANGE 包合電線断面積 AWG#20-#16 0.51~1.38 mm ²	INSULATION DIA 被覆外径 1.9~3.4 mmφ	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 耗
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC ±—

1 PLC ±—

2 PLC ±—

3 PLC ±—

4 PLC ±—

ANGLES ±—

FINISH
仕上

SEE TABLE

GENERAL TOLERANCE
一般公差

10 ≥ : ±0.2

30 ≥ > 10: ±0.25

100 ≥ > 30: ±0.3

ANGLES: ±3°

MATERIAL
材料

SEE TABLE

DWN

M.SUZUKI

04AUG1998

CHK

H.TAGUCHI

04AUG1998

APVD

H.TAGUCHI

04AUG1998

PRODUCT SPEC
製品規格

108-5126

APPLICATION SPEC
取付適用規格

114-5041

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

NAME
名称

187 SERIES POSITIVE LOCK MARK II REC.

187シリーズポジティブロック(マークII)リセブタクル

SIZE

CAGE CODE

DRAWING NO
番号

RESTRICTED TO

A300779

C=170325

SCALE
尺度

5:1

SHEET

1 of 1

REV

J

1470-19 (3/11)