

PART NUMBER: EMS050120-P5P-SZ

DESCRIPTION: switching power supply

Features

- Energy Star and California Energy Commission Regulations compliant
- RoHS Compliant
- Interchangeable input plugs
- 100-240 V ac input
- Regulated output voltage
- Over-voltage protected
- Short-circuit protected
- UL/cUL certified and FCC class B compliant



INPUT

rated input voltage	100 V ~ 240 V ac
input voltage range	90 V ~ 264 V ac
rated frequency	50~60 Hz
frequency range	47~63 Hz
rated input current	300 mA RMS max.
inrush current	15 A max. at 115 / 30 A max. at 230 V ac cool start
no load power consumption	0.3 W max. (CEC Compliant)

OUTPUT

output voltage	5 V dc at 1.2 A
output min. current	0 A
line regulation	± 1%
load regulation	± 5%
over voltage protection	10 V dc max. (output shut down)
short circuit protection	output shut down and auto restart
ripple voltage	100 mV (p-p) (100~240 V ac at full load)
efficiency	Energy Star Compliant - Efficiency Level IV

SAFETY & EMI

HI-POT	input to output	3000 V ac or 4242 V dc at 10 mA for 1 min.
insulation resistance	input to output	> 100 M Ohm at 500 V dc
safety approvals	UL/cUL, CE, GS	
EMI standard	FCC class B, EN55022	
RoHS compliant	yes	
leakage current	0.25 mA	


ENVIRONMENTAL

storage temperature	-10°C ~ +70° C
operating temperature	0°C ~ +40° C
storage humidity	10~90%
operating humidity	20~80%

PART NUMBER: EMS050120-P5P-SZ

DESCRIPTION: switching power supply

LABEL




PART NUMBER: EMS050120-P5P-SZ

DESCRIPTION: switching power supply

MECHANICAL DRAWING


input plug	Interchangeable PIN (UL, UK, VDE, SAA)
weight	150 g
case size	64 L x 40.5 W x 30 H mm Tolerance: ± 1



PART NUMBER: EMS050120-P5P-SZ

DESCRIPTION: switching power supply

DC CORD



#20AWGX2C UL2468 HAVE ON WORD WIRE IN OUTER, NO WORD WIRE IN INNER

OD: Ø1.9*3.8




Parameter request	
a. ±50°	VIBRATION TEST
b. WEIGHT 200g	
c. 40 ROUND/MINUTE	
d. OVER 1000 COUNT MIN	

PART NUMBER: EMS050120-P5P-SZ

DESCRIPTION: switching power supply

INDIVIDUAL PACKAGING

tolerance: ± 1



PART NUMBER: EMS050120-P5P-SZ

DESCRIPTION: switching power supply

PACKAGING

tolerance: +7/-0

CARTON INTERNAL SIZE: 450*308*300mm
Q'TY: 80PCS(20*4)
"RoHS Compliant"

