




DIN 912

ISO 4762

8.8

Standard withdrawn



## BN 272

## Hex socket head cap screws

fully threaded

Steel 8.8

black

- ~UNI 5931
- ~ČSN 021143

[3D Cadenas](#)

M18; M22; M27: not included in ISO 4762

| Article# | d <sub>1</sub> | d <sub>2</sub> | k | s   | t min. | L    |
|----------|----------------|----------------|---|-----|--------|------|
| 1000004  | M3             | 5,5            | 3 | 2,5 | 1,3    | 4    |
| 1000012  |                |                |   |     |        | 5    |
| 1000020  |                |                |   |     |        | 6    |
| 1000039  |                |                |   |     |        | 8    |
| 1000047  |                |                |   |     |        | 10   |
| 1000055  |                |                |   |     |        | 12   |
| 1000063  |                |                |   |     |        | (14) |
| 1000071  |                |                |   |     |        | 16   |
| 1301780  |                |                |   |     |        | (18) |
| 1301799  |                |                |   |     |        | 20   |
| 2108178  |                |                |   |     |        | (22) |
| 3054493  |                |                |   |     |        | 25   |
| 1000152  | M4             | 7              | 4 | 3   | 2      | 5    |
| 1000160  |                |                |   |     |        | 6    |
| 1000179  |                |                |   |     |        | 8    |
| 1000187  |                |                |   |     |        | 10   |
| 1000195  |                |                |   |     |        | 12   |
| 1000209  |                |                |   |     |        | (14) |
| 1000217  |                |                |   |     |        | 16   |
| 1000225  |                |                |   |     |        | (18) |
| 1000233  |                |                |   |     |        | 20   |
| 1301802  |                |                |   |     |        | (22) |
| 1301810  |                |                |   |     |        | 25   |
| 3054499  |                |                |   |     |        | 30   |
| 1000330  | M5             | 8,5            | 5 | 4   | 2,5    | 6    |
| 1000349  |                |                |   |     |        | 8    |

M18; M22; M27: not included in ISO 4762

| Article# | d <sub>1</sub> | d <sub>2</sub> | k | s | t min. | L    |
|----------|----------------|----------------|---|---|--------|------|
| 1000357  | M5             | 8,5            | 5 | 4 | 2,5    | 10   |
| 1000365  |                |                |   |   |        | 12   |
| 1000373  |                |                |   |   |        | (14) |
| 1000381  |                |                |   |   |        | 16   |
| 1000403  |                |                |   |   |        | (18) |
| 1000411  |                |                |   |   |        | 20   |
| 1000438  |                |                |   |   |        | (22) |
| 1000446  |                |                |   |   |        | 25   |
| 1000454  |                |                |   |   |        | 30   |
| 3054504  |                |                |   |   |        | 35   |
| 8147744  |                |                |   |   |        | 40   |
| 1000551  | M6             | 10             | 6 | 5 | 3      | 6    |
| 1000578  |                |                |   |   |        | 8    |
| 1000586  |                |                |   |   |        | 10   |
| 1000594  |                |                |   |   |        | 12   |
| 1000608  |                |                |   |   |        | (14) |
| 1000616  |                |                |   |   |        | 16   |
| 1000624  |                |                |   |   |        | (18) |
| 1000632  |                |                |   |   |        | 20   |
| 1000640  |                |                |   |   |        | (22) |
| 1000659  |                |                |   |   |        | 25   |
| 1000667  |                |                |   |   |        | 30   |
| 1874640  |                |                |   |   |        | 35   |
| 1000675  |                |                |   |   |        | 40   |
| 3378226  |                |                |   |   |        | 45   |
| 1000683  |                |                |   |   |        | 50   |
| 3054507  |                |                |   |   |        | 60   |
| 1000845  | M8             | 13             | 8 | 6 | 4      | 10   |
| 1000853  |                |                |   |   |        | 12   |
| 1000861  |                |                |   |   |        | (14) |
| 1000888  |                |                |   |   |        | 16   |
| 1000896  |                |                |   |   |        | (18) |
| 1000918  |                |                |   |   |        | 20   |
| 1000926  |                |                |   |   |        | (22) |
| 1000934  |                |                |   |   |        | 25   |
| 1000942  |                |                |   |   |        | 30   |
| 1000950  |                |                |   |   |        | 35   |
| 1000969  |                |                |   |   |        | 40   |
| 1000977  |                |                |   |   |        | 45   |
| 1000985  |                |                |   |   |        | 50   |
| 1000993  |                |                |   |   |        | 60   |

M18; M22; M27: not included in ISO 4762

| Article# | d <sub>1</sub> | d <sub>2</sub> | k  | s  | t min. | L    |
|----------|----------------|----------------|----|----|--------|------|
| 3054588  | M8             | 13             | 8  | 6  | 4      | 70   |
| 8093202  | M10            | 16             | 10 | 8  | 5      | 10   |
| 1001213  |                |                |    |    |        | 12   |
| 1001221  |                |                |    |    |        | (14) |
| 1001248  |                |                |    |    |        | 16   |
| 1001256  |                |                |    |    |        | (18) |
| 1001264  |                |                |    |    |        | 20   |
| 1001272  |                |                |    |    |        | (22) |
| 1001280  |                |                |    |    |        | 25   |
| 1001299  |                |                |    |    |        | 30   |
| 1001302  |                |                |    |    |        | 35   |
| 1001310  |                |                |    |    |        | 40   |
| 8089876  |                |                |    |    |        | 45   |
| 1001329  |                |                |    |    |        | 50   |
| 1001337  |                |                |    |    |        | 60   |
| 3054589  |                |                |    |    |        | 70   |
| 1001582  | M12            | 18             | 12 | 10 | 6      | 16   |
| 1001590  |                |                |    |    |        | (18) |
| 1001604  |                |                |    |    |        | 20   |
| 1001612  |                |                |    |    |        | (22) |
| 1001620  |                |                |    |    |        | 25   |
| 1001639  |                |                |    |    |        | 30   |
| 1001647  |                |                |    |    |        | 35   |
| 1001655  |                |                |    |    |        | 40   |
| 1301829  |                |                |    |    |        | 45   |
| 1001663  |                |                |    |    |        | 50   |
| 1542273  |                |                |    |    |        | 60   |
| 3054683  |                |                |    |    |        | 70   |
| 1001914  | (M14)          | 21             | 14 | 12 | 7      | 25   |
| 1001922  |                |                |    |    |        | 30   |
| 1001930  |                |                |    |    |        | 35   |
| 1001949  |                |                |    |    |        | 40   |
| 1001957  |                |                |    |    |        | 45   |
| 1301837  |                |                |    |    |        | 50   |
| 1301845  |                |                |    |    |        | 55   |
| 1002155  | M16            | 24             | 16 | 14 | 8      | 25   |
| 1002163  |                |                |    |    |        | 30   |
| 1002171  |                |                |    |    |        | 35   |
| 1002198  |                |                |    |    |        | 40   |
| 1002201  |                |                |    |    |        | 45   |
| 1002228  |                |                |    |    |        | 50   |

M18; M22; M27: not included in ISO 4762

| Article# | d <sub>1</sub> | d <sub>2</sub> | k  | s  | t min. | L   |
|----------|----------------|----------------|----|----|--------|-----|
| 1301853  | M16            | 24             | 16 | 14 | 8      | 55  |
| 1471279  |                |                |    |    |        | 60  |
| 3054690  |                |                |    |    |        | 70  |
| 1002473  | (M18)          | 27             | 18 | 14 | 9      | 35  |
| 1002481  |                |                |    |    |        | 40  |
| 1002503  |                |                |    |    |        | 45  |
| 1002511  |                |                |    |    |        | 50  |
| 1002538  |                |                |    |    |        | 55  |
| 1301861  |                |                |    |    |        | 60  |
| 5402823  | M20            | 30             | 20 | 17 | 10     | 30  |
| 1002643  |                |                |    |    |        | 35  |
| 1002651  |                |                |    |    |        | 40  |
| 1002678  |                |                |    |    |        | 45  |
| 1002686  |                |                |    |    |        | 50  |
| 1002694  |                |                |    |    |        | 55  |
| 1002708  |                |                |    |    |        | 60  |
| 1301888  |                |                |    |    |        | 65  |
| 1479016  |                |                |    |    |        | 70  |
| 3054698  |                |                |    |    |        | 80  |
| 1002937  | (M22)          | 33             | 22 | 17 | 11     | 40  |
| 1002945  |                |                |    |    |        | 45  |
| 1002953  |                |                |    |    |        | 50  |
| 1002961  |                |                |    |    |        | 55  |
| 1002988  |                |                |    |    |        | 60  |
| 1301896  |                |                |    |    |        | 70  |
| 1003100  | M24            | 36             | 24 | 19 | 12     | 40  |
| 1003119  |                |                |    |    |        | 50  |
| 1003127  |                |                |    |    |        | 55  |
| 1003135  |                |                |    |    |        | 60  |
| 1003143  |                |                |    |    |        | 70  |
| 1301918  |                |                |    |    |        | 75  |
| 1301926  |                |                |    |    |        | 80  |
| 1003348  | (M27)          | 40             | 27 | 19 | 13,5   | 70  |
| 1301934  |                |                |    |    |        | 80  |
| 1301942  |                |                |    |    |        | 90  |
| 1003437  | M30            | 45             | 30 | 22 | 15,5   | 60  |
| 1805533  |                |                |    |    |        | 70  |
| 1003445  |                |                |    |    |        | 80  |
| 1542281  |                |                |    |    |        | 100 |
| 1003569  | M36            | 54             | 36 | 27 | 19     | 80  |
| 1143778  |                |                |    |    |        | 90  |

M18; M22; M27: not included in ISO 4762

| Article# | d <sub>1</sub> | d <sub>2</sub> | k  | s  | t min. | L   |
|----------|----------------|----------------|----|----|--------|-----|
| 1003577  | M36            | 54             | 36 | 27 | 19     | 100 |