MALLORY Mallory Sonalert Products Inc.	Part # PT-2038FW
Sales Outline Drawing	Revision A

OBSOLETE- USE PT-2038FWQ

Specificati

Resonant Frequency (Hz)	3800 ± 500
Operating Voltage Max (Vdc)	3 ~ 28
Rated Voltage (Vdc)	12
Current Consumption Max. (mA)	8 at Rated Voltage
Sound Pressure Level Min. (dB)	85 at 30cm at Rated Voltage
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 707 UL94HB plastic resin (Color: Black)
Leading Wire	32 AWG
Weight (Grams)	2.0
Options	For other options contact factory

Dimensions: (units: mm)



4411 South High School Road, Indianapolis, Indiana 46241 USA ● Phone (317) 612-1000 ● Fax (317) 612-1010 ● http://www.mallory-sonalert.com