Part Number: 25-02-1118

2.54mm Pitch C-Grid® Header, Dual Row, Shrouded, with PC Slot and Guide Ear, 118 Circuits, 0.76µm Gold (Au) Selective Plating



Series image - Reference only

Status:	Planned for Obsolescence
Series:	70204
Category:	PCB Headers
Overview:	C-Grid® Products

Go to **Part Detail**▼

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Email this page

Mates With Part(s):
71973

Specifications & Other Documents:

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling
Check our list of old tooling that used to be available for this part

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

EU ELV:
EU RoHS: Compliance Status Not Reviewed
China RoHS:
REACH SVHC: Not Reviewed
Low-Halogen Status: Not Reviewed

RoHS Certificate of Compliance (PDF)
Multiple Part Product Compliance Form

Part Detail

COLLAPSE ALL

General

Status	**Planned for Obsolescence**
Category	PCB Headers
Series	70204
Application	Board-to-Board, Signal
Overview	C-Grid® Products
Product Name	C-Grid®
UPC	800754562751

Physical

Breakaway	No
Circuits (Loaded)	118
Circuits (maximum)	118
Durability (mating cycles max)	50
Glow-Wire Compliant	No
Guide to Mating Part	Yes
Lock to Mating Part	None
Material - Plating Mating	Gold
Number of Rows	2
Orientation	Vertical
PC Tail Length	2.79mm
PCB Locator	No
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical

(Please review the Product Specification for specific details.)	
Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

Material Info

Copyright 2015