P1,P2:	M-Y337A
	M-337A

Customer No: No:14



PART NO.	Length "L"	Length "X"
101265	1800mm	1840mm
101260	900mm	940mm

* NOTE:All revlvent materials are complied with RoHS directive.



No.	DESCRIPTION	Q'TY	Supplier
4	BLACK HEAT SHRINK TUBE 1.0*15mm	2	M743
	PE HOOD COLOR TRANSPARENT	2	M304
	COPPER FOIL 33*90mm	2	M583
	COPPER FOIL 7.5*55mm	2	M583
	MOLDED PE COLOR TRANSPARENT		M280
	MOLDED PVC BLACK		M304
3	UL20276 34 TWISTED PAIRS 30AWG, ALUM-MYLAR AND COPPER BRAID FOIL SHIELDING WITH DRAIN WIRE, OD 9.8, JACKET BLACK	Xmm	M298
2	SCREW 5*38.5mm	4	M95
1	U2CN68 MALE, GOLD FLASH ON CONTACTS, WHITE INSULATOR	2SET	M83

APPROVED		MSL ENTERPRISES CORP.	Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm; 201~1000mm ±20mm; 1001 ~1500mm ±25mm; 1501~2100mm ±30mm; 2100mm↑ ±40mm
CHECKED	HU		
DRAWING	MEI		
DATE	27/MAY/10	ITEM NO. 3154-3	UNIT:mm

1 RE.1 2010.05.27	ADD LENGTH	CHECKED	