About Leviton
A Century of Success
Press
Join Our eMailing List
Trade Shows
RoHS
Career Opportunities
Contact Us
All Leviton Products
Electrical
Network Solutions
Lighting Controls
Entertainment
Home Automation
Connected Home
Energy Management
Power Quality
Library Home
Application Notes
Brochures / Catalogs
Case Studies
DDLs
Downloads
Drawings
Line Cards
Manuals / Instructions
Product Specifications / Datasheets
Software
Specs (AIA / CSI)
Take One
Tech Notes
Technical Articles
Videos
ez-Biz
ez-Find
ez-Learn
ez-Configurator
Distribution Home
Contractor Connection
ez-Learn
ez-Find
Sign In - B2B
OEM Home
How to Buy
Whats New
Press/News
Retail Home
Product Information
How To
Merchandising
Energy Smart Living
International Home
China (English)
China (Chinese)
Mexico (English)
Mexico (Spanish)
Middle East (English)
International Contact
Press
Products
Trade Shows
Made to Order
EZE-Rough
Acenti Devices
AC Switches
Appliance Switches
Architectural Controls
Camera Systems
Combination Devices
Connectors & Cables
Cord Sets
Corrosion Resistant Devices
Daylighting Controls
Decora Devices
Dimmers
Cam-Type Devices
Electrical Accessories
Entertainment Accessories
Entertainment Fixtures
Entertainment Lighting Controls
Entertainment Lighting Kits

> Electrical
> Network Solutions
> Lighting Controls
> Entertainment
> Home Automation
> Connected Home
> Energy Management
> Power Quality

5824I

ZOOM

Quantity: 1

Color: Ivory

LC IMG EE COLOR

NEMA: 6-20R

LC IMG EE NEMA

5824-I

Description

20 Amp, 250 Volt, NEMA 6-20R, 2P, 3W, Narrow Body Duplex Receptacle, Straight Blade, Commercial Grade, Self Grounding, , , Back & Side Wired, Steel Strap, - Ivory

Additional Product Information

- Dimensional Drawing
- Wiring Diagram

Product Features

Grounding: Self Grounding
Amperage: 20 Amp
Voltage: 250 Volt
NEMA: 6-20R
Pole: 2
Wire: 3
Termination: Back & Side
Face Material: Nylon
Body Material: Nylon
Strap Material: Steel
Color: Ivory
Standards and Certifications: UL/CSA
Warranty: 10 Year Limited

AC Horsepower Ratings	
At Rated Voltage:	2 HP

Electrical Specifications	
Dielectric Voltage:	Withstands 2000V per UL498
Current Limiting:	Full Rated Current
Temperature Rise:	Max 30C after 100 cycles OL at 150 percent rated current

Environmental Specifications	
Flammability:	Rated V-2 per UL94
Operating Temperature:	-40C to 60C

Material Specifications	
Face Material:	Nylon
Body Material:	Nylon
Line Contacts:	Brass Triple-Wipe .031 Thick
Terminal Screws:	Brass 10-32
Grounding Screw:	Brass 8-32
Yoke:	Zinc-Plated Steel
Clamp Nuts:	Zinc-Plated Steel
Ground Clips:	Brass-Plated

Mechanical Specifications	
Terminal ID:	Brass-Hot, Green-Ground, White-Neutral
Terminal Accom.:	14-10 AWG
Product ID:	Ratings are permanently marked on device

Standards and Certifications	
NEMA:	WD-2 WD-6
ANSI:	C-73
UL498:	File E13399
UL Fed Spec WC-596:	File E13399
CSA C22.2 No. 42:	File 152105
NOM:	057

© 2006-2009 Leviton Manufacturing Co., Inc. All rights reserved.