

CAPACITANCE	3000pF GMV
TEMP. RANGE	-55°C TO +125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	125°C 200 VDC
DC RESISTANCE	.01 Ohms MAX.

I.L.@25°C, NO LOAD

13

FREQ. MHz	I.L. (dB)
10MHz	5dB
100MHz	45dB
1GHz	70dB
10GHz	70dB

SCHEMATIC



MARKING:

PART: S003

BAG PACK: SCI 1250-003
DATE CODE
LOT No.
QTY./BAG (200 MAX.)

NOTES:
1. MAX INSTALLATION TORQUE: 4in-lbs.
2. HARDWARE IS INCLUDED.

REV. NO.	CHANGE NOTICE
13	CN #11628
12	CN 208567
11	CN 186587
10	CN 176833
9	CN 175872
8	CN 166807
7	CN 161800
6	CN 154611
5	CN 153682
4	CN 152986
3	CN 148961
2	CN 148903
1	CN 147402
0	CN 147308

TOLERANCES UNLESS OTHERWISE SPECIFIED
Fractions ± 1/64
Dec. .xx±
Dec. .xxx± .010
Angles ±0° 30'
CODE IDENT. NO. OLSP2

api technologies corp.
FAIRVIEW PENNSYLVANIA

Dwn. KEVERLINE
Date 3-11-15
Engr. B.DEVINE
Scale NONE

Description
FLTR, SING, Pi, BSHG

1250-003