THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2009
© COPYRIGHT 2009 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C13	ECN-21-126515	16NOV2021	OH	JZ
	D	ECR-24-212401	29MAY 24	A.M	J.Z
	D1	ECN-20250912-003	18SEP25	R.Y	J.Z





VERSION WITHOUT LOCKING FLAG 3-1823468-X

SAME DIMENSION APPLY AS FOR 1823468-X VERSIONS















VERSION WITH CPA AND ALTERNATIVE DESIGN

VERS.	COD	TE-NO	REV	MATERIAL	COLOR	DESCRIPTION	WEIGHT (g)	ITEM NO
H	0-2309220-9	A	PBT-GF10	RED	CPA, ...	8.7	4
			MVQ	LIGHT BLUE	RADIAL SEAL ...		3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	GREY	6POS., CAVITY 2 CLOSED		1
H	4-2309220-8	A	PBT-GF10	RED	CPA, ...	8.7	4
			MVQ	LIGHT BLUE	RADIAL SEAL ...		3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	GREY	6POS., CAVITY 3 CLOSED		1
H	5-2309220-8	A	PBT-GF10	RED	CPA, ...	8.7	4
			MVQ	LIGHT BLUE	RADIAL SEAL ...		3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	GREY	6POS., CAVITY 4 CLOSED		1
H	2-2309220-8	A	PBT-GF10	RED	CPA, ...	8.7	4
			MVQ	LIGHT BLUE	RADIAL SEAL ...		3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	GREY	6POS., ...		1
G	9-2309220-7	A	PBT-GF10	RED	CPA, ...	8.7	4
			MVQ	LIGHT BLUE	RADIAL SEAL ...		3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	GREEN	6POS., ...		1
F	2-2309220-6	A	PBT-GF10	RED	CPA, ...	8.7	4
			MVQ	LIGHT BLUE	RADIAL SEAL ...		3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	WHITE	6POS., ...		1
E	2-2309220-5	A	PBT-GF10	RED	CPA, ...	8.7	4
			MVQ	LIGHT BLUE	RADIAL SEAL ...		3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	BLUE	6POS., ...		1
D	2-2309220-4	A	PBT-GF10	RED	CPA, ...	8.7	4
			MVQ	LIGHT BLUE	RADIAL SEAL ...		3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	ORANGE	6POS., ...		1
C	2-2309220-3	A	PBT-GF10	RED	CPA, ...	8.7	4
			MVQ	LIGHT BLUE	RADIAL SEAL ...		3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	RED	6POS., ...		1
B	2-2309220-2	A	PBT-GF10	RED	CPA, ...	8.7	4
			MVQ	LIGHT BLUE	RADIAL SEAL ...		3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	DARK BROWN	6POS., ...		1
A	2-2309220-1	A	PBT-GF10	RED	CPA, ...	8.5	4
			MVQ	LIGHT BLUE	RADIAL SEAL ...		3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	BLACK	6POS., ...		1

VERSION WITHOUT LOCKING FLAG AND WITHOUT CPA



VERS.	COD	TE-NO	REV	MATERIAL	COLOR	DESCRIPTION	WEIGHT (g)	ITEM NO
H	3-1823467-8	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	GREY	6POS., ...		1
G	3-1823467-7	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	GREEN	6POS., ...		1
F	3-1823467-6	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	WHITE	6POS., ...		1
E	3-1823467-5	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	BLUE	6POS., ...		1
D	3-1823467-4	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	ORANGE	6POS., ...		1
C	3-1823467-3	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	RED	6POS., ...		1
B	3-1823467-2	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	DARK BROWN	6POS., ...		1
A	3-1823467-1	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	7.8	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	BLACK	6POS., ...		1

VERSION WITH CPA



VERS.	COD	TE-NO	REV	MATERIAL	COLOR	DESCRIPTION	WEIGHT (g)	ITEM NO
H	8-1823467-8	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8.5	4
			PBT-GF10	VIOLET	RETAINER, ...		3
			PA66	GREY	6POS., CAVITY 3 CLOSED		2
			PBT-GF10	RED	CPA, ...		1
H	9-1823467-8	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8.5	4
			PBT-GF10	VIOLET	RETAINER, ...		3
			PA66	GREY	6POS., CAVITY 4 CLOSED		2
			PBT-GF10	RED	CPA, ...		1
H	1-1823467-8	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8.5	4
			PBT-GF10	VIOLET	RETAINER, ...		3
			PA66	GREY	6POS., ...		2
			PBT-GF10	RED	CPA, ...		1
G	1-1823467-7	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8.5	4
			PBT-GF10	VIOLET	RETAINER, ...		3
			PA66	GREEN	6POS., ...		2
			PBT-GF10	RED	CPA, ...		1
F	1-1823467-6	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8.5	4
			PBT-GF10	VIOLET	RETAINER, ...		3
			PA66	WHITE	6POS., ...		2
			PBT-GF10	RED	CPA, ...		1
E	1-1823467-5	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8.5	4
			PBT-GF10	VIOLET	RETAINER, ...		3
			PA66	BLUE	6POS., ...		2
			PBT-GF10	RED	CPA, ...		1
D	1-1823467-4	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8.5	4
			PBT-GF10	VIOLET	RETAINER, ...		3
			PA66	ORANGE	6POS., ...		2
			PBT-GF10	RED	CPA, ...		1
C	1-1823467-3	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8.5	4
			PBT-GF10	VIOLET	RETAINER, ...		3
			PA66	RED	6POS., ...		2
			PBT-GF10	RED	CPA, ...		1
B	1-1823467-2	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8.5	4
			PBT-GF10	VIOLET	RETAINER, ...		3
			PA66	DARK BROWN	6POS., ...		2
			PBT-GF10	RED	CPA, ...		1
A	1-1823467-1	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8.3	4
			PBT-GF10	VIOLET	RETAINER, ...		3
			PA66	BLACK	6POS., ...		2
							1

VERSION WITHOUT CPA



VERS.	COD	TE-NO	REV	MATERIAL	COLOR	DESCRIPTION	WEIGHT (g)	ITEM NO
H	8-1823467-8	A	MVQ	LIGHT BLUE	RADIAL SEAL ...	9	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	GREY	6POS., CAVITY 3 CLOSED		1
H	9-1823467-8	A	MVQ	LIGHT BLUE	RADIAL SEAL ...	9	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	GREY	6POS., CAVITY 4 CLOSED		1
H	1823467-8	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	GREY	6POS., ...		1
G	1823467-7	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	GREEN	6POS., ...		1
F	1823467-6	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	WHITE	6POS., ...		1
E	1823467-5	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	BLUE	6POS., ...		1
D	1823467-4	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	ORANGE	6POS., ...		1
C	1823467-3	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	RED	6POS., ...		1
B	1823467-2	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	DARK BROWN	6POS., ...		1
A	1823467-1	C	MVQ	LIGHT BLUE	RADIAL SEAL ...	7.8	3
			PBT-GF10	VIOLET	RETAINER, ...		2
			PA66	BLACK	6POS., ...		1

CODING "A" BLACK SCHWARZ	
CODING "B" DARK BROWN DUNKELBRAUN	
CODING "C" RED ROT	
CODING "D" ORANGE ORANGE	
8-1823467-8 CAVITY-3 CLOSED	 1.25
4-2309220-8 CAVITY-3 CLOSED	
5-2309220-8 CAVITY-4 CLOSED	
2-2309220-8 ALL CAVITY OPEN	
CODING "E" BLUE BLAU	
CODING "F" WHITE WEISS	
CODING "G" GREEN GRUEN	
CODING "H" GREY GRAU	
9-1823467-8 CAVITY-4 CLOSED	 1.25
0-2309220-9 CAVITY-2 CLOSED	
D1 9-1823467-1 ALL CAVITY OPEN	

NOTES
Bemerkungen

1. DELIVERY CONDITION, RETAINER IN PER-LOCK POSITION
Anlieferungszustand, Kontaktsicherung in Vorrastellung

2. TERMINALS, SEE TE DRAWING 1241436
Kontakte, siehe TE Zeichnung 1241436

3. INTERFACE ACC. TO TE SPECIFICATION No. 114-18375-1
Schnittstelle nach TE Spizifikation Nr. 114-18375-1

4. BULK PACKAGED
Schuttgut verpackt

THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN	18MAY2009	TE Connectivity
	CHK Ashour	19MAY2009	
	H. Ripper		
DIMENSIONS: mm	APVD		NAME 6POS. AMP MCP1.5K, REC. HOUSING 6POLIG. AMP MCP1.5K, BUCHSENGEHAEUSE ASSY
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.5; 1 PLC ±0.5; 2 PLC ±0.5; 3 PLC ±-; 4 PLC ±-; ANGLES ±1°; FINISH -	PRODUCT SPEC -		
	APPLICATION SPEC -		SIZE A0 / CAGE CODE 00779 / DRAWING NO C-1823467 / RESTRICTED TO
MATERIAL S.TAB. -	WEIGHT -		
	CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 2 / REV D1

4806 (3/13)

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2009
© COPYRIGHT 2009 BY - ALL RIGHTS RESERVED.

REVISIONS					
F	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			







9-1823467-1
UNSPECIFIED DIMENSIONS FOLLOW 1823467-8
EXCEPT THE DIMENSION SHOWN BELOW

5:1









VERS.	COD	TE-NO	REV	MATERIAL	COLOR	DESCRIPTION	WEIGHT (g)	ITEM NO
VERSION WITH (FA AND ALTERNATIVE DESIGN	H	9-1823467-1	A	PBT-GF10	RED	CPA, ...	7,8	4
				MVQ	LIGHT BLUE	RADIAL SEAL ...		3
				PBT-GF10	VIOLET	RETAINER, ...		2
				PA66	GREY	6POS, ...		1



VERS.	COD	TE-NO	REV	MATERIAL	COLOR	DESCRIPTION	WEIGHT (g)	ITEM NO
VERSION WITH (FA AND ALTERNATIVE DESIGN	H	1-2309220-9	A	PBT-GF10	RED	CPA, ...	8,7	4
				MVQ	LIGHT BLUE	RADIAL SEAL ...		3
				PBT-GF10	VIOLET	RETAINER, ...		2
				PA66	GREY	6POS, CAVITY 2 CLOSED		1
	H	4-2309220-9	A	PBT-GF10	RED	CPA, ...	8,7	4
				MVQ	LIGHT BLUE	RADIAL SEAL ...		3
				PBT-GF10	VIOLET	RETAINER, ...		2
				PA66	GREY	6POS, CAVITY 3 CLOSED		1
	H	5-2309220-9	A	PBT-GF10	RED	CPA, ...	8,7	4
				MVQ	LIGHT BLUE	RADIAL SEAL ...		3
				PBT-GF10	VIOLET	RETAINER, ...		2
				PA66	GREY	6POS, CAVITY 4 CLOSED		1
	H	2-2309220-9	A	PBT-GF10	RED	CPA, ...	8,7	4
				MVQ	LIGHT BLUE	RADIAL SEAL ...		3
				PBT-GF10	VIOLET	RETAINER, ...		2
				PA66	GREY	6POS, ...		1



VERS.	COD	TE-NO	REV	MATERIAL	COLOR	DESCRIPTION	WEIGHT (g)	ITEM NO
VERSION WITHOUT CPA	H	8-1823467-9	A	MVQ	LIGHT BLUE	RADIAL SEAL ...	9	3
				PBT-GF10	VIOLET	RETAINER, ...		2
				PA66	GREY	6POS, CAVITY 3 CLOSED		1
	H	6-1823467-9	A	MVQ	LIGHT BLUE	RADIAL SEAL ...	9	3
				PBT-GF10	VIOLET	RETAINER, ...		2
				PA66	GREY	6POS, CAVITY 4 CLOSED		1
	H	4-1823467-9	A	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
				PBT-GF10	VIOLET	RETAINER, ...		2
				PA66	GREY	6POS, ...		1
	G	4-1823467-7	A	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
				PBT-GF10	VIOLET	RETAINER, ...		2
				PA66	GREEN	6POS, ...		1
	F	4-1823467-6	A	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
				PBT-GF10	VIOLET	RETAINER, ...		2
				PA66	WHITE	6POS, ...		1
	E	4-1823467-5	A	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
				PBT-GF10	VIOLET	RETAINER, ...		2
				PA66	BLUE	6POS, ...		1
	D	4-1823467-4	A	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
				PBT-GF10	VIOLET	RETAINER, ...		2
				PA66	ORANGE	6POS, ...		1
	C	4-1823467-3	A	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
				PBT-GF10	VIOLET	RETAINER, ...		2
				PA66	RED	6POS, ...		1
	B	4-1823467-2	A	MVQ	LIGHT BLUE	RADIAL SEAL ...	8	3
				PBT-GF10	VIOLET	RETAINER, ...		2
				PA66	DARK BROWN	6POS, ...		1
	A	4-1823467-1	A	MVQ	LIGHT BLUE	RADIAL SEAL ...	7,8	3
				PBT-GF10	VIOLET	RETAINER, ...		2
				PA66	BLACK	6POS, ...		

CODING "A"
BLACK
SCHWARZ



CODING "B"
DARK BROWN
DUNKELBRAUN



CODING "C"
RED
ROT



CODING "D"
ORANGE
ORANGE



8-1823467-8
CAVITY-3 CLOSED



4-2309220-8
CAVITY-3 CLOSED



5-2309220-8
CAVITY-4 CLOSED



2-2309220-8
ALL CAVITY OPEN



CODING "E"
BLUE
BLAU



CODING "F"
WHITE
WEISS



CODING "G"
GREEN
GRUEN



CODING "H"
GREY
GRAU



9-1823467-8
CAVITY-4 CLOSED



0-2309220-9
CAVITY-2 CLOSED



D1
9-1823467-1
ALL CAVITY OPEN



NOTES
Bemerkungen

1 DELIVERY CONDITION. RETAINER IN PER-LOCK POSITION
Anlieferungszustand. Kontaktsicherung in Vorraststellung

2 TERMINALS. SEE TE DRAWING: 1241436
Kontakte. Siehe TE Zeichnung 1241436

3 INTERFACE ACC. TO TE SPECIFICATION No. 114-18375-1
Schnittstelle nach TE Spizifikation Nr. 114-18375-1

4 BULK PACKAGED
Schuttgut verpackt

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0.5
1 PLC ±0.5
2 PLC ±0.5
3 PLC ±-
4 PLC ±-
ANGLES ±1°

MATERIAL S.TAB.
FINISH -
-

DWN Y. Ashour 18MAY2009
CHK H. Ripper 19MAY2009
APVD
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME 6POS. AMP MCP1.5K, REC. HOUSING
6POLIG. AMP MCP1.5K, BUCHSENGEHAEUSE
ASSY

SIZE A0 | CAGE CODE 00779 | DRAWING NO C-1823467 | RESTRICTED TO -

CUSTOMER DRAWING | SCALE 2:1 | SHEET 2 OF 2 | REV D1

4806 (3/13)