REVISIONS						
REV	ZONE	ECO	DESCRIPTION	DATE	BY	APPR
A1	--	--	RELEASE NUMBER	02/09/12	--	--
A2	--	C0081S	CHANGE NOTES	03/02/13	JARRY	--







安费诺精密连接器(深圳)有限公司
Amphenol PCD Shenzhen
受 控 文 件
2013 年 2 月 25 日





注(NOTES):

1. 材料 Material.
   绝缘体:热缩性塑料,UL 94V-0;
   Insert: thermoplastic,UL 94V-0;
   颜色:ATP04-2P=灰色,ATP04-2P-BLK=黑色
   Color:ATP04-2P=Gray,ATP04-2P-BLK=Black
2. 工作温度Operation temperature:-55° C～+125° C;
3. 性能参数 Specification:
   3.1额定电压Rating Voltage: 250VAC MAX;
   3.2额定电流Rating current: 25A;
   3.3耐电压Withstanding voltage: 1500VAC;
   3.4绝缘电阻Insulation resistance: 1000MΩ;
   3.5接触电阻Contact resistance: 10mΩ;
   3.6防水等级Waterproof: IP67;
   3.7机械寿命Mating cycles: 100 cycles;
4. 互配产品:ATP06-2S-XXXX (XXXX=所有扩展料号);
   Mating part:ATP06-2S-XXXX (XXXX=All Extended Part);
5. 与产品互配的端子和线缆规格Mating contacts and wire.

CONTACT SIZE	MIN.INSUL O.D	MAX.INSUL O.D	WIRE RANGE
12	3.35	4.20	10～14AWG

A2

ITEM	PART NUMBER	Qty	DESCRIPTION	REMARK

MATERIALS LIST

UNLESS OTHERWISE SPECIFIED
1) All dimensions are in metric(mm).
2) Tolerances are as follows:
1 PL DEC ±0.30
2 PL DEC ±0.15 Fractions ±1/64
3 PL DEC ±0.08 Angles ±1°

MATERIAL SPECIFICATIONS:

PROCESS SPECIFICATIONS:

签 名 SIGNATURE		日期 DATE
制 图 DRAWN	JARRY	03/02/13
审 核 CHECKED	Orion Li	
工 艺 ENGINEER		
批 准 APPROVAL	Tommy xie	2013.02.22 ~~21:33:30 +08'00'~~
客 户 CUSTOMER		

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

SINE Systems Corporation
A Subsidiary of Amphenol Corporation

Assembly Connector Receptacle,2 way

DWG NO: ATP04-2P-XXX

第三角投影 THIRD ANGLE PROJECTION	文件编号 FSCM NO.	幅 面 SIZE	质 量 MASS	版次 REV.	比 例 SCALE
		A3		A2	X:X

SHEET 1 OF 1 NEXT ASS'Y: