Female Header Micro Match SMD 1,27 mm

Series **374**



Rated current	1,5 A
Rated voltage	230 VRMS / VDC
Withstand voltage	500 VRMS for one minute
Material contact	Phosphor bronze
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +105°C
Max. processing temper.	260°C for 10 seconds

All dimensions in mm.

pitch **1,27**

termination

max. pincount **026**

Product group **4**

Variation

Without locking feature



With locking feature



PCB Layout





	no. of contacts	see figure left	see figure left	see figure left	available in variation
	n	A	B	C	
1	004	7,00	3,81	5,60	1
	006	9,54	6,35	8,14	1
	008	12,08	8,89	10,68	1
	010	14,62	11,43	13,22	1
	012	17,16	13,97	15,76	1
	014	19,70	16,51	18,30	1
	016	22,24	19,05	20,84	1
	018	24,78	21,59	23,38	1
	020	27,32	24,13	25,92	1
	022	29,86	26,67	28,46	1
	024	32,40	29,21	31,00	1
	026	34,94	31,75	33,54	1
2	004	9,70	3,81	5,60	2
	006	12,24	6,35	8,14	2
	008	14,78	8,89	10,68	2
	010	17,32	11,43	13,22	2
	012	19,86	13,97	15,76	2
	014	22,40	16,51	18,30	2
	016	24,94	19,05	20,84	2
	018	27,48	21,59	23,38	2
	020	30,02	24,13	25,92	2
	022	32,56	26,67	28,46	2
	024	35,10	29,21	31,00	2
	026	37,64	31,75	33,54	2

Plating:
T = Sn

Packaging:
R = Reel
T = Tube

Cap:
0 = Without cap
1 = With cap

Variation (1,2) | No. of contacts | Plating contact | Packaging (R,T) | Cap (0,1)

Order code: 374-?-???-0-NTX-K??

GARRY

www.mpe-connector.de

CS130212_V3

Mating series	373	372
see page	3-19	6-5

MPE-Garry GmbH • Schäfflerstraße 13 • 87629 Füssen • Germany • Phone: +49 (0) 83 62 / 91 56-0 • Fax: +49 (0) 83 62 / 91 56-500 • Email: vk@mpe-connector.de • www.mpe-connector.de