


REV.	DATE	DESCRIPTION
A	05/22/03	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
8						DRAWN	G.R.S.						05/22/03
7						CHECKED							
6						ISSUED			PART DESCRIPTION				
5	CONTACT PIN	BRASS	GOLD	1					SMA .141” SEMI-RIGID PLUG (FOR MICRO COAX – UT 141A-AL-TP-LL)				
4	INSULATOR	TEFLON	NATURAL	1					PART NO.				
3	GASKET	SILICONE	RED	1					132102-10				
2	RETAINER RING	BER. COPPER	NATURAL	1									
1	SHELL/BODY	BRASS	GOLD	1									
DESCRIPTION		MATERIAL	FINISH	QTY	CAD FILE		DWG. NO.		REV.	SIZE	SCALE		
					C:/132/132102-10.DWG		132102-10.DWG		NC	A	NA		