

**T&B Catalog Number:****LTC075****UPC Number:**

78621078955

**Description:**

3/4" PVC Industrial Grade Type B smooth non-metallic liquidtight conduit; color-Black. For use with Bullet#174; Liquidtight Fittings.

**Status:**

Active

**Features**

Fast installation, even in tight or cramped spaces.

Smooth inner diameter allows easy wire pulling.

Smooth outer jacket uses material approved for outdoor use, is sunlight resistant and oil resistant.

Lightweight and liquidtight.

**General**

Material	PVC
Color	Black
Conduit Size (inches)	3/4
Recommended industrial applications	Machine tools, motor hookups, food processing equipment, extensions from wire ways, and sensor and micro switch wiring found in control consoles.

**Dimension Information**

I.D. - Minimum (inches)	0.820
I.D. - Maximum (inches)	0.840
O.D. - Minimum (inches)	1.030
O.D. - Maximum (inches)	1.050

**Packaging**

T&B Order Multiple	100
Package in Units	100
T&B Sold in UOM	Feet
T&B Weight Per UOM	21.6 lbs. per 100

**Application Support**

Guide to Nonmetallic Conduit Applications Available on Website

XTRAFLEX System Specifications Available on Website

**Notes**

*Note	XTRAFLEX#174; Type B Conduit, LTC series only, suitable for hazardous location where general purpose equipment is specifically permitted by the NEC Class I Div 2; Class II Div 1 & 2; Class III Div 1 & 2, NEC Article 501-4(b), 502-4(a)(b); and 503-3(a)(b).
-------	---

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**

File Nbr:

E 95745

**For further technical assistance, please contact us...**

