



## Armored Cable/Flexible Metal Conduit Fittings

**T&B Catalog Number:**

302-TB

**UPC Number:**

78621000302

**Status:**

Active

**Description:**

1/2 in. Tite-Bite Connector, Steel-Electro Zinc Plated.

### Features

Easy to install with double grip saddle, connectors are completely salvageable.

### Application

For use with Armored Cable and Flexible Metal Conduit.

To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

### General

Trade Size (inches)	1/2
Material	Steel
Finish	Electro Zinc Plated

### Dimension Information

Dimension A (inches)	1 5/8
Dimension B (inches)	1 11/16
Dimension C (inches)	1 7/64
Knockout Size (inches)	1/2
Cable Opening-Minimum (inches)	0.75
Cable Opening-Maximum (inches)	0.937

### Specifications

3dmodel	Available on Website
---------	----------------------

### Packaging

T&B Inner Pack	50
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	12.19 lbs. per 100

### Notes

UL Listed for metal clad cable (MCI)

UL listed for new interlocked armor ground type metal clad cable (MCI-A)

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:

E 23018

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289

